©Trelleborg Printing Solutions TCS 022015CN

vulcan® Royal Form

关键特性

- 背胶橡皮布
- 确保高质量印刷
- 减少纸边痕
- 超长使用寿命
- 特殊胶涂层，拆卸方便干净

主要应用

标签，表格印刷，上光

厚度：0.90/0.95/1.00/1.05毫米



Vulcan Royal Form

参数指标

油墨适性	传统油墨
橡胶表面颜色	蓝色
厚度 （毫米）	0.90/0.95/1.00/1.05毫米
平均载荷量 N/cm2 0.23mm凹痕	250
表面粗糙度（Ra micro）	0.8
最大线性伸长(%)	不适用
抗拉伸强度（N/mm）	不适用
底布加强 - 防水/溶剂性能	不适用
附加信息	
表层橡胶	提供UV印刷表面供选择（Royal Form UV）

The information contained in this document is intended to provide guidance. The information is NOT a specification and all figures in the document are nominal.
This document and the information it contains do not create any warranties for any product and Trelleborg Printing Solutions disclaims any warranty of merchantability or fitness for a particular purpose for the product described in this document. This document discloses information that is proprietary to Trelleborg Printing Solutions. The receipt or possession of the document does not confer any right to reproduce or disclose the document, any information contained in it, or any physical article or device, or to practice any method or process except by written agreement with Trelleborg Printing Solutions. Trelleborg Printing Solutions is committed to the ongoing development of its products. For that reason, Trelleborg Printing Solutions reserves the right to alter the actual specifications of its products without prior notice.

TRELLEBORG

WWW.TRELLEBORG.COM/PRINTING

For more information:
Visit us: www.trelleborg.com/printing
Email us: printing@trelleborg.com
Twitter: twitter.com/PrintingInsight
Youtube: youtube.com/user/PrintingInsights
Call us +86 21 5131 3183/ 5131 3157