©Trelleborg Printing Solutions TCS 022015CN

vulcan® Easy Plus

关键特性

- 优秀的整体印刷质量和网点重现
- 优良的条杠吸收性能
- 优秀的抗冲击能力
- 优秀的回弹能力

主要应用

商业，包装印刷

厚度：1.96毫米

Vulcan Easy Plus

参数指标

油墨适性	传统油墨
橡胶表面颜色	蓝色
厚度 （毫米）	1.96
平均载荷量 N/cm2 0.23mm凹痕	250
表面粗糙度（Ra micro）	1.2
最大线性伸长(%)	<0.9
抗拉伸强度（N/mm）	>60
底布加强 - 防水/溶剂性能	否
附加信息	
油墨转移	适合使用传统油墨的普通印刷客户

The information contained in this document is intended to provide guidance. The information is NOT a specification and all figures in the document are nominal.
This document and the information it contains do not create any warranties for any product and Trelleborg Printing Solutions disclaims any warranty of merchantability or fitness for a particular purpose for the product described in this document. This document discloses information that is proprietary to Trelleborg Printing Solutions. The receipt or possession of the document does not confer any right to reproduce or disclose the document, any information contained in it, or any physical article or device, or to practice any method or process except by written agreement with Trelleborg Printing Solutions. Trelleborg Printing Solutions is committed to the ongoing development of its products. For that reason, Trelleborg Printing Solutions reserves the right to alter the actual specifications of its products without prior notice.

TRELLEBORG

WWW.TRELLEBORG.COM/PRINTING

For more information:
Visit us: www.trelleborg.com/printing
Email us: printing@trelleborg.com
Twitter: twitter.com/PrintingInsight
Youtube: youtube.com/user/PrintingInsights
Call us +86 21 5131 3183/ 5131 3157