

NPC Waterstop Grouting Ring

SIZING CHART

Pipe Size (inches)	Type of Pipe	Pipe O.D.	P/N	Clamp P/N	Clamp Qty.
10"	PVC	10.50	WS-10105	I-190	2
	Ductile Iron	11.10	WS-11115	I-218	2
	Quality Culvert	11.50	WS-11115	I-218	2
	ADS/Hancor	11.63	WS-11512	I-218	2
12"	PVC	12.50	WS-12125	I-218	2
	Ductile Iron	13.20	WS-13135	I-242	2
	JM Eagle	14.25	WS-14145	I-258	2
	Baughman	14.50	WS-14515	I-258	2
	Quality Culvert	14.56	WS-14515	I-258	2
	ADS/Hancor	14.63	WS-14515	I-258	2
15"	PVC	15.30	WS-15516	I-282	2
	JM Eagle	17.50	WS-17518	I-306	2
	Truss	17.00	WS-16517	I-306	2
	Quality Culvert	17.70	WS-17518	I-306	2
	ADS/Hancor	17.75	WS-17518	I-306	2
	Baughman	18.25	WS-18185	I-306	2
16"	Ductile Iron / Cast Iron	17.40	WS-17518	I-306	2
18"	PVC	18.70	WS-18519	I-318	2
	Ductile Iron / Cast Iron	19.50	WS-19195	I-348	2
	JM Eagle	20.875	WS-21215	I-180	4
	Quality Culvert	21.15	WS-21215	I-180	4
	Baughman	21.21	WS-21215	I-180	4
	ADS/Hancor	21.44	WS-21522	I-180	4
	RCP-B Wall	23.00	WS-22523	I-190	4
20"	Ductile Iron / Cast Iron	21.60	WS-21522	I-180	4
21"	PVC	22.05	WS-21522	I-190	4
	RCP-B Wall	26.50	WS-2627	I-218	4
24"	PVC	24.80	WS-24525	I-218	4
	Ductile Iron / Cast Iron	25.80	WS-2526	I-218	4
	JM Eagle	27.50	WS-2728	I-242	4
	Quality Culvert	27.76	WS-2728	I-242	4
	ADS/Hancor	28.00	WS-2728	I-242	4
	Baughman	28.50	WS-2829	I-242	4
	RCP-B Wall	30.00	WS-2930	I-258	4
	RCP-C Wall	31.50	WS-3132	I-282	4

SIZING CHART

Pipe Size (inches)	Type of Pipe	Pipe O.D.	P/N	Clamp P/N	Clamp Qty.
27"	PVC	27.95	WS-2728	I-242	4
	RCP-B Wall	33.50	WS-3334	I-282	4
30"	Ductile Iron / Cast Iron	32.00	WS-3132	I-282	4
	JM Eagle	34.63	WS-3435	I-282	4
	Quality Culvert	35.40	WS-3536	I-306	4
	ADS	35.50	WS-3536	I-306	4
	Hancor	35.50	WS-3536	I-306	4
	Baughman	35.65	WS-3536	I-306	4
	RCP-B Wall	37.00	WS-3637	I-306	4
	RCP-C Wall	38.50	WS-3839	I-318	4
36"	Ductile Iron / Cast Iron	38.30	WS-3839	I-318	4
	Baughman	41.50	WS-4142	I-348	4
	JM Eagle	41.50	WS-4142	I-348	4
	ADS/Hancor	41.88	WS-4142	I-348	4
	Quality Culvert	41.90	WS-4142	I-348	4
	RCP-B Wall	44.00	WS-4344	I-242	6
	RCP-C Wall	45.50	WS-4546	I-258	6
42"	JM Eagle	47.38	WS-4748	I-256	6
	ADS	48.19	WS-4849	I-282	6
	Quality Culvert	48.20	WS-4849	I-282	6
	Baughman	48.20	WS-4849	I-282	6
	Hancor	48.44	WS-4849	I-282	6
	RCP-C Wall	52.50	WS-5253	I-306	6
48"	Ductile Iron / Cast Iron	50.80	WS-5051	I-282	6
	JM Eagle	53.81	WS-5354	I-242	6
	Hancor	54.19	WS-5455	I-306	6
	Baughman	54.30	WS-5455	I-306	6
	Quality Culvert	54.40	WS-5455	I-306	6
	RCP-B Wall	58.00	WS-5758	I-318	6



TRELLEBORG

WWW.TRELLEBORG.COM/PIPE-SEALS