



TrellTent[®] 2/2 L

A lightweight tent with great flexibility!



- ▲ With the aid of a high-pressure fan, the tent can be raised in less than five minutes.
- ◀ Low weight, removable arches and windows in the roof are characteristic features of our new lightweight tent.

The lightweight TT 2/2 L tent is a further development of our standard tents

Greater flexibility

Our new lightweight tent is a further development of our classic TrellTent®, which we have been producing for over two decades. It has been developed according to the wishes of our customers for a lighter tent which is more suited to civilian needs. In addition, we have taken away some of the details normally included in a TrellTent® and instead produced a wide range of accessories. In this way, you can adapt the tent and the equipment to suit your own needs.

Removable arches

One great difference from our standard tents is that the lightweight tent is fitted with removable arches which are attached with Velcro tape. Since the arches are attached for normal use, no great difference is noticed when raising the tent. The advantage is instead the potential for flexibility offered by removable arches. With the aid of our range of accessories, you can equip the tent with as many mounting lugs as you need and place them exactly where you want them. If the tent should become damaged or excessively worn, there is always the possibility of reusing the arches and replacing the tent canvas and its welded floor.

Easy to raise

The lightweight tent is easy to store and transport. Thanks to its low weight, it is also easy to carry, and it can be raised in just 5–10 minutes with a high-pressure fan.


Easy to use

When the tent is raised, you have a sheltered workplace which is easy to heat and offers good hygiene. The lightweight tent can be used as a hospital tent, a command centre, a temporary workplace, a camp, etc. In other words, it can be used in any place, at any time it is needed. Lightweight tents can also be connected in a row with the aid of our accessories kit, which means that the work area can be adjusted to suit the needs.

Accessories

Guy ropes	069 350 200
Tent pegs	075 000 600
Bag for tent pegs	483 021 002
Mallet sledge hammer	077 702 100
Loose inner floor	483 032 002
Mounting lugs	
grommet belt	484 722 001
Plastic chain	483 139 003
Air distribution	
channels ducts	483 138 002
High-pressure fan	483 300 002
Foot pump	483 119 005
Connection unit	438 045 050

We also offer heaters, lighting and screen printing as desired.



FACT BOX TrellTent® 2/2 L

Material:	PVC-coated fabric
Colours:	Yellow exterior, light green interior
Dimensions:	5.2 x 6.3 m, 33.3 m ²
Height:	2.6 m
Dimensions when packed:	1.0 x 0.8 x 0.8 m
Weight:	108 kg



Trelleborg Protective Products AB, Box 1520, SE-271 00 Ystad, Sweden
Tel: +46 411 679 40. Fax: +46 411 152 85
E-mail: protective@trellborg.com Internet: www.trelleborg.com/protective

Local distributor: