

Kor-N-Seal[®] II

306 Series Pipe-to-Manhole Connector



- *Allows you to fit large diameter pipe into the smallest possible manhole structures*
- *Can be used in cored or formed holes*
- *Meets the specifications of ASTM C923*
- *Easy-to-install*



The Patented 4" wide Stainless Steel Korbond is able to overcome the curvature of smaller sized manholes and provide a watertight seal.



Kor-N-Seal II

306 Series Pipe-to-Manhole Connector

The Kor-N-Seal II 306 Series pipe-to-manhole connector lets you fit larger pipe into the smallest possible manhole. When you put a hole into a manhole, the sides of the hole are further back than the top and bottom because of the curvature of the manhole.

The patented NPC 4 inch wide stainless steel Korband is able to overcome the curvature of the manhole and provide a watertight seal.

As an example, where a regular boot would require a 60 inch manhole for pipe with a 30 inch O.D., the 306 Series Kor-N-Seal allows you to use a standard 48 inch manhole with a 5 inch wall. This is possible because of our patented 4 inch wide stainless steel Korband.

Connector P/N	Pipe O.D. Range	Hole Size Range	Min. Manhole Diameter/Wall Thickness
S306-22 S306-22L	17.625 - 19.000 19.000 - 19.625	21.98 - 22.13	36/4
S306-24 S306-24L	19.625 - 21.000 21.000 - 21.625	23.98 - 24.13	36/4
S306-26 S306-26L	21.625 - 23.000 23.000 - 23.625	26.00 - 26.20	36/4
S306-28 S306-28L	23.625 - 25.000 25.000 - 25.625	28.00 - 28.20	48/5
S306-30 S306-30L	25.625 - 27.000 27.000 - 27.625	30.00 - 30.20	48/5
S306-32 S306-32L	27.625 - 29.000 29.000 - 29.625	32.00 - 32.20	48/5
S306-34 S306-34L	29.625 - 31.000 31.000 - 31.625	34.00 - 34.20	48/5

Connector P/N	Pipe O.D. Range	Hole Size Range	Min. Manhole Diameter/Wall Thickness
S306-36 S306-36L	31.625 - 33.000 33.000 - 33.625	36.00 - 36.20	60/6
S306-38 S306-38L	33.625 - 35.000 35.000 - 35.625	38.00 - 38.20	60/6
S306-40 S306-40L	35.625 - 37.000 37.000 - 37.625	40.00 - 40.20	60/6
S306-42 S306-42L	37.625 - 39.000 39.000 - 39.625	42.00 - 42.20	72/7
S306-44 S306-44L	39.625 - 41.000 41.000 - 41.625	44.00 - 44.20	72/7
S306-46 S306-46L	41.625 - 43.000 43.000 - 43.625	46.00 - 46.20	72/7
S306-48 S306-48L	43.625 - 45.000 45.000 - 45.625	48.00 - 48.20	72/7

Using Corrugated Pipe - Adapters are required when using Corrugated Pipe. Refer to the Corrugated Pipe Adapter Data Sheet for details.

Covered under U.S. Patent No. 6,641,176



Trelleborg Pipe Seals Milford, Inc.
P.O. Box 301, 250 Elm Street, Milford, New Hampshire 03055 U.S.A.
Tel: 800-626-2180 603-673-8680 Fax: 603-673-7271 www.trelleborg.com/npc