

ALIKLER D

AGRI & FOOD

Foodstuff transfer



Applications

High pressure discharge of liquid foods-tuffs such as milk, beer, oil, fat, wine, cider, fruit juice, and alcohol up to 96 %.

Suction on unloading bays in dairies.

Equipment of processing and filling plants, and liquid foodstuff tankers.

Advantages

- Smooth, seamless, white, multipurpose food grade tube that does not propagate bacterial growth.
- Able to recover its shape after accidental squeeze.
- Changes in temperature have little effect due to the qualities of the rubber compound.
- Resistant to cleaning with detergents at temperatures up to 130 °C (during several minutes).
- Non-marking, abrasion resistant cover.
- Contains no phthalate.

Technical description

Inner tube: food grade, oil resistant NBR, white, smooth.

Reinforcement: synthetic textile with embedded PET helix for ID ≥ 50 mm.

Cover: oil and weather resistant NBR/PVC, blue, fabric impression.

Temperature range: - 30 °C to + 100 °C.

Standard/Approval:

EU regulation n° 1935/2004.

FDA regulation 21 CFR 177.2600.

German legislation: BfR recommendation XXI cat. 2.

French legislation.

All relevant migrations tests (France and FDA) were performed and confirmed compliant by the French institute of Poitiers (IANESCO).

Couplings/Fittings

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

ALIKLER D

23/12/2009

ID	OD	Working pressure	Bursting pressure	Max vacuum	Bending radius	Weight	Length	Article number	Stock (■) or min. order
mm	mm	bar	bar	bar	mm	kg/m	m		m
32.0	-0/+1 44.0 ±1.5	15	40	0.7	220	1.00	20	0061567	■
							40	0061568	■
38.0	-0/+1 51.0 ±1.5	15	40	0.7	265	1.20	20	0061569	■
							40	0061570	■
50.0	-0/+1 66.0 ±1.5	15	40	0.7	300	1.97	20	0061571	■
							40	0061572	■
63.0	-0/+1 79.0 ±1.5	15	40	0.7	450	2.38	20	0061573	■
							40	0061574	■
75.0	-0/+1 91.0 ±1.5	15	40	0.7	525	2.85	20	0061575	■
							40	0061576	■
100.0	-0/+1 117.0 ±1.5	15	40	0.7	700	3.81	20	0061577	■
							40	0061578	■

Branding



and embossed: TRELLEBORG - ALIKLER D - ND - WP 15 bar - week/year - Made in France

