

# PERFORMER BLOC-END® COUPLING

## Coupling for material handling hoses

CONSTRUCTION & MINING EQUIPMENT

### Abrasive materials hydraulic and pneumatic handling


Connection of the PERFORMER GL AD10H, PERFORMER GL AD10P, PERFORMER GL AD10T.

#### Advantages

- Hoses can be cut to length on site or at manufacture to suit the specific installation requirements.
- Easy to cut: no special tooling is needed as the coupling face acts as a cutting guide.
- The flange can be adjusted easily for fitting and will not deform in service.
- Quick and easy to replace.
- The couplings can be removed from a damaged hose and reused on replacement.
- A lightweight connection system.

#### Technical description

Standardised drilling.  
 ID≤150mm: WP 10bar.  
 ID>150mm: WP 5bar.



Complete BLOC-END® coupling. With half shells, gasket and bolts/nuts/washers.		Spare part-kit. 2 half shells without gaskets and bolts.	Spare part-kit. 2 gaskets.	Bolt, including nut and washer.	
PN10/PN20		PN10/PN20	PN10/PN20		
ID hose mm	Article number	Article number	Article number	Number of bolts	Article number /piece
25	<b>5103109</b>	<b>0195500</b>	<b>5103110</b>	4	<b>5103113</b>
32	<b>5103111</b>	<b>0195501</b>	<b>5103112</b>	4	<b>5103113</b>
40	<b>0117042</b>	<b>0116890</b>	<b>0116966</b>	4	<b>0111322</b>
50	<b>0117043</b>	<b>0116891</b>	<b>0116967</b>	4	<b>0111322</b>
65	<b>0117044</b>	<b>0116893</b>	<b>0116968</b>	4	<b>0111322</b>
80	<b>0117045</b>	<b>0116895</b>	<b>0116969</b>	4	<b>0111322</b>
100	<b>0117046</b>	<b>0116897</b>	<b>0116970</b>	4	<b>0111322</b>
125	<b>0117047</b>	<b>0116899</b>	<b>0116971</b>	4	<b>0111322</b>
150	<b>0117048</b>	<b>0116901</b>	<b>0116972</b>	4	<b>0111322</b>
200	<b>0117049</b>	<b>0116902</b>	<b>0116973</b>	6	<b>0111322</b>
250	<b>0118093</b>	<b>0118089</b>	<b>0118087</b>	6	<b>0111322</b>
300	<b>0118095</b>	<b>0118091</b>	<b>0118088</b>	6	<b>0111322</b>
350	<b>5101097 *</b>	<b>5100847</b>	<b>5100848</b>	6	<b>5102957</b>
400	<b>5102956</b>	<b>5102955</b>	<b>5102953</b>	6	<b>5102957</b>

Article numbers in bold = stock item. Other article numbers = non stock (consult us).

\* Only PN10 for ID 350mm.

Assembly of 2 BLOC-END® per hose length (ID 25 to 150mm)

Assembly of 2 BLOC-END® per hose length (ID 200 to 250mm)

Assembly of 2 BLOC-END® per hose length (ID 300 to 400mm)