



Lateral Connection Rehabilitation

FROM THE MAIN TO
THE HOUSE IN JUST ONE STEP

epros® DrainMth™

epros® DrainMth™ System

- Rehabilitation system for lateral connections pipes including the transition to the main-pipe, operating from the main sewer to the house
- No-Dig method
- No need to enter private property
- Main pipe diameter: DN 150 (rehabilitated approx. DN 135) – DN 600 / 6" – 24"
- Lateral diameter: DN 100 – DN 250 / 4" – 10"
- Connection angle: 30° – 90°
- Rehabilitation length: approx. 30 m / 98 ft
- Max. line distance between access manhole and lateral junction: 150 m / 492 ft
- Easy to position
- Excellent mechanical properties
- No subsequent cutting required
- General technical approval from German DIBt
- Patented system components
- Now with temperature measured at the LinerEndCap (liner end)

Rehabilitates
both laterals and their connections
without the need of building access
and in just one work step

4 Packer Types:

Type 0:	DN 135 – 150 / 5“ – 6“
Type I:	DN 200 – 225 / 8“ – 9“
Type II:	DN 250 – 350 / 10“ – 14“
Type III:	DN 400 – 600 / 16“ – 24“

epros® DrainMth Liner „Basic“

- 100 % polyester fibre – flexible material
- One side PP coated
- 100 % steam resistant
- Negotiates bends up to 45°

epros® DrainMth Liner „Stretch“

In preparation:

- Negotiates bends up to 90°
- Allows for up to 2 changes in dimension

Technical Approval

German Institute for
Structural Engineering
DIBt-Nr. Z-42.3-468
DN 100 to DN 600
with resin system HC120/HC 120+





Trelleborg is a world leader in engineered polymer solutions that seal, damp and protect critical applications in demanding environments. Our innovative engineered solutions accelerate performance for customers in a sustainable way. The Trelleborg Group has local presence in over 40 countries around the world.

Trelleborg Pipe Seals is a world leading supplier of new and rehabilitation sealing solutions for concrete and plastic pipes and manholes used for water, sewerage and drainage.

We deliver continuous innovation to customers across the globe, with a logistics and sales network. Comprising the most advanced polymer technology, our high performance seals ensure fulfillment of the highest possible reliability standards.

WWW.TRELLEBORG.COM/PIPE-SEALS



facebook.com/pages/Trelleborg-Pipe-Seals-Duisburg

twitter.com/PipeSeals

youtube.com/c/TrelleborgPipeSeals

<http://bit.ly/2q4rirl>



Headquarters:

Trelleborg Pipe Seals Duisburg GmbH, Dr.-Alfred-Herrhausen-Allee 36, 47228 Duisburg, Germany, Phone: +49 2065 999 0, Fax: +49 2065 999 111

Pipeline Rehabilitation Products,

North America, c/o Trelleborg Pipe Seals Milford Inc, 250 Elm Street Milford, New Hampshire 03055, USA, Tel: +1 603 673 8680, Fax: +1 603 673 7271