


Focus on packaging Chapter 2



Blankets for offset printing on packaging
Trelleborg Printing Solutions' copyright


Vulcan blanket choice by application

	EASY PLUS	ZENITH	COMBO PLUS	FOLIO UV	SUNRISE	KART ONE	KART ONE UV	DECO	PACK	PACK UV	SUPER UV	IRIO
PACKAGING	X	X	X	X	X	X	X					
METAL DECORATING								X	X	X	X	
SPECIALITY												X cold foil
INK	Conventional	Hybrid	Hybrid	UV	UV	Hybrid	UV	Conventional	Conventional	UV	UV	-
TOP COMPOUND	NBR	NBR	NBR	EPDM	EPDM	NBR	EPDM	NBR	NBR	EPDM	EPDM	
THICKNESS +/- 0.02 mm.	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm 1.70mm
ROUGHNESS	0.90 - 1.15 µm	0.40 - 0.80 µm	0.40 - 0.80 µm	0.60 - 1.00 µm	0.60 - 1.00 µm	0.40 - 0.80 µm	0.60 - 1.00 µm	1.20 - 1.60 µm	0.60 - 1.00 µm	1.10 - 1.70 µm	0.60 - 1.00 µm	N.A.
LOAD Kg/cm ²	250	250	250	250	250	150	150	600	400	400	400	250
PLY	3	3	3	3	3	3	3	3	3	3	3	4 or 3

Rollin blanket choice by application

Rollin	GRAFFITY	POLYCELL PLUS	PEAK	COMPACT	SUNTECH	METRO	UV-E	METAL UV
PACKAGING	x	X	X	X	X	X	X	
METAL DECORATING						X	X	X
INK	Hybrid	Hybrid	Hybrid	Hybrid	UV	Conventional	UV	UV
TOP COMPOUND	NBR	NBR	NBR	NBR	EPDM	NBR	EPDM	EPDM
THICKNESS +/- 0.02 mm.	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm
ROUGHNESS	0.80 - 1.20 μm	0.60 - 1.00 μm	0.60 - 1.00 μm	0.40 - 0.80 μm	0.40 - 0.80 μm	0.90 - 1.50 μm	0.60 - 1.00 μm	0.60 - 1.00 μm
LOAD Kg/cm²	250	250	250	250	250	250	250	250
PLY	3	3	3	3	3	3	3	3

Printec blanket choice by application

	574	864	334	814	205	263	414	624
PACKAGING	X	X	X					
METAL DECORATING				X	X	X		
SPECIAL APPLICATIONS							Plasticpot	Plasticpot
INK	Conventional	Conventional	UV	Hybrid	UV	Conventional	Hybrid	Hybrid
TOP COMPOUND	NBR	NBR	EPDM	NBR	EPDM	NBR	NBR	NBR
THICKNESS +/- 0,02 mm.	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95 mm	1.95mm 1.96mm 1.98 mm	1.96 mm	1.96 mm
ROUGHNESS	0.70 - 1.30 µm	0.70 - 1.30 µm	0.70 - 1.30 µm	0.70 - 1.30 µm	0.70 - 1.30 µm	0.70 - 1.30 µm	0.40 - 0.70 µm	N.A
LOAD Kg/cm ²	150	140	115	125	150	115	N.A.	N.A
Ply	4	3	3	4	4	3	4	4



TRELLEBORG

Email us printingsm@trelleborg.com

Chapter 3: soon available