



HPS Solidflex
Traction

HPS Solidflex
Smooth

HPS Smooth

PREMIUM CONSTRUCTION SOLID

BRAWLER HPS SKID STEER

The Brawler HPS (High Performance Solid) Skid Steer tires are designed to perform in extreme environments including scrap metal recycling, waste transfer stations and mining operations.

The Brawler HPS Solidflex features elliptical apertures to deliver a comfortable ride resulting in reduced equipment and operator fatigue.

FEATURES AND BENEFITS

- Excellent traction
- Durable cut-resistant rubber compound eliminates downtime caused by flats and sidewall cuts
- Press on to flat-based wheels
- Deep lug tread design offers three times more wear than a pneumatic tire
- Steel base rings ensure strict rim adherence

APPLICATIONS

- Waste Transfer Stations
- Metal Recycling
- Construction & Demolition
- Steel Mills & Foundries
- Heavy Industrial
- Quarries and Open Pit Mining
- Underground Mining

PREMIUM CONSTRUCTION SOLID

**BRAWLER HPS
SKID STEER****HPS SOLIDFLEX TRACTION**

Tire Size	Pneumatic Equivalent Size	Rim Size	Overall Diameter [mm]	Section Width [mm]	Tread Depth [mm]	Load Capacity 10 km/h [kg]
30x10-16	10-16.5	6.00-16	759	236	44	3000
31x10-20	10-16.5	7.5-20	785	254	41	2815
33x12-20	12-16.5	7.5-20	840	284	56	2970
36x14-20	14-17.5	7.5-20	915	356	71	3310
40x14-20	15-19.5	10.0-20	1015	356	94	4955

HPS SOLIDFLEX SMOOTH

Tire Size	Pneumatic Equivalent Size	Rim Size	Overall Diameter [mm]	Section Width [mm]	Tread Depth [mm]	Load Capacity 10 km/h [kg]
31x10-20	10-16.5	7.5-20	785	254	41	2815
33x12-20	12-16.5	7.5-20	840	284	56	2970
36x14-20	14-17.5	7.5-20	915	356	71	3310
40x14-20	15-19.5	10.0-20	1015	356	94	4955

HPS SMOOTH

Tire Size	Pneumatic Equivalent Size	Rim Size	Overall Diameter [mm]	Section Width [mm]	Tread Depth [mm]	Load Capacity 10 km/h [kg]
31x10-20	10-16.5	7.5-20	785	254	41	3755
33x12-20	12-16.5	7.5-20	840	305	56	3960
36x14-20	14-17.5	7.5-20	915	356	71	4415
40x14-20	15-19.5	10.0-20	1015	356	94	6605

**Notes: Tread depth on smooth tires indicates wearable rubber.
All Brawler™ HPS tires are available as either an assembly or as tire only.**

**TRELLEBORG**

WWW.TRELLEBORG.COM/WHEELS