



SK-900

SK-900 ND

PREMIUM CONSTRUCTION PNEUMATIC **SK-900 & SK-900 ND** SKID STEER

The SK-900 premium tire is designed for use in heavy duty applications.

The SK-900 ND (Non-Directional) is designed for maximum performance on concrete, asphalt and other hard surfaces.

These tires have a wide lug tread pattern that provides optimal grip and traction on both smooth and rough surface. The high quality compound promotes maximum tire life and increased cut and chip resistance.

FEATURES AND BENEFITS

- Natural rubber
- Extended tire life
- High stability / maximum safety
- Optimal grip and traction

APPLICATIONS

- Deeper tread than a standard skid steer tire for better wear
- Flat profile with reinforced sidewalls for maximum protection
- Tread design pull equally when going forward or in reverse

PREMIUM CONSTRUCTION PNEUMATIC

SK-900**SKID STEER LOADER**

Tire Size	Alternative Size	Ply Rating	Rim Size	Tire Type	Dimensions [mm]			Skid Steer at 10 km/h	
					Overall Diameter	Section Width	Tread Depth	Inflation Pressure [bar]	Load Capacity [kg]
23x8.5-12		12	7.0-12	Tubeless	579	213	12	7.30	1250
27x10-12	250/75-12	14	8.00G-12	Tubeless	690	255	18	7.00	3540
27x10.5-15		16	W8.0-15	Tubeless	691	259	13	7.10	1800
29x12.5-15		8	10.0-15	Tubeless	742	310	18	3.20	1530
31x15.5-15		8	13.0-15	Tubeless	792	391	20	3.10	1975
10-16.5		8	8.25-16.5	Tubeless	773	264	19	4.10	1880
10-16.5		10	8.25-16.5	Tubeless	773	264	19	5.20	2135
31.5x13-16.5		10	9.75-16.5	Tubeless	790	326	20	4.90	2575
12-16.5		10	9.75-16.5	Tubeless	831	307	17	4.50	2540
12-16.5		12	9.75-16.5	Tubeless	831	307	17	5.50	2865
14-17.5		14	10.50-17.5	Tubeless	921	349	22	5.50	3875
15-19.5		14	11.75-19.5	Tubeless	1019	389	22	4.80	4565

PREMIUM CONSTRUCTION PNEUMATIC

SK-900 ND**SKID STEER LOADER**

Tire Size	Ply rating	Rim Size	Tire Type	Dimensions [mm]			Skid Steer at 10 km/h	
				Overall Diameter	Section Width	Tread Depth	Inflation Pressure [bar]	Load Capacity [kg]
10-16.5	10	8.25-16.5	Tubeless	773	264	27	5.20	2135
12-16.5	12	9.75-16.5	Tubeless	831	307	33	5.50	2865

**TRELLEBORG**

WWW.TRELLEBORG.COM/WHEELS