



Brawler HPS Tough jobs, soft ride.



Maximum comfort
and durability


Protecting people protecting assets

Delivering the smoothest ride in the Brawler range, Trelleborg's Brawler HPS Soft Ride tires are designed to perform in tough recycling and waste management applications. The Soft Ride compound combined with Brawler's unique elliptical sidewall apertures delivers higher

shock absorption and reduced vibration, ensuring the best possible protection for operators and machines. Brawler HPS Soft Ride offers both the toughness of a traditional solid tire and the ride comfort of a filled pneumatic tire.


Vibration & Comfort – Dynamic Test

TESTED TO ISO 5008



Deflection – Static Test

DEFORMATION (MM) UNDER VARIABLE LOAD



Brawler HPS Soft Ride



ANTI VIBRATION CONSTRUCTION
Enhanced driver comfort



CUT RESISTANT COMPOUND
Damage protection



ELLIPTICAL APERTURES
Increased deflection



ULTRA DEEP TREAD
Extended service life

Why choose Soft Ride?



MAXIMUM VALUE
Reduced operating cost per hour



MAXIMUM UPTIME
Increased productivity, maintenance free



INCREASED SAFETY
Reduced driver exposure to vibration



REDUCED IMPACT
Protecting people, protecting assets

Brawler HPS Soft Ride

PREMIUM OTR SOLID



HPS Solidflex
Traction

HPS Solidflex
Smooth

HPS SOLIDFLEX TRACTION

Tire Size	Alternative Size	Rim Size	Overall Diameter [mm]	Section Width [mm]	Tread Depth [mm]	Load Capacity 10 km/h [kg]
17.5-25	445/80-25	14.0-25	1340	446	155	8805
20.5-25	525/80-25	17.0-25	1495	527	188	12155
23.5-25	605/80-25	19.5-25	1630	606	216	15320
26.5-25	685/80-25	22.0-25	1715	718	236	18295
29.5-25	-	25.0-25	1845	761	264	22540

HPS SOLIDFLEX SMOOTH

Tire Size	Alternative Size	Rim Size	Overall Diameter [mm]	Section Width [mm]	Tread Depth [mm]	Load Capacity 10 km/h [kg]
17.5-25	445/80-25	14.0-25	1340	446	155	8805
20.5-25	525/80-25	17.0-25	1495	527	188	12155
23.5-25	605/80-25	19.5-25	1630	606	216	15320
26.5-25	685/80-25	22.0-25	1715	718	236	18295
29.5-25	-	25.0-25	1845	761	264	22540

**Notes: Tread depth on smooth tires indicates wearable rubber.
All Brawler™ HPS tires are available as either an assembly or as tire only.**



TRELLEBORG



Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheels