



HD Solidflex Smooth

HD Smooth

# Brawler HD Loader

PREMIUM OTR SOLID

Brawler HD tires are designed to perform in extreme applications such as scrap metal recycling centers, waste transfer stations and mining operations.


These tires feature a two-piece patented wheel and disk system that allows tire and wheel interchangeability by simply changing the disk.

Brawler HD tires are available aperture free or with elliptical apertures (Solidflex).

### Main Benefits

- Up to 3 times more wearable rubber than standard pneumatic tires
- Comfortable ride when compared to foam-filled pneumatic tires
- Steel wheels engineered with the strength and flexibility to handle overloads, excessive torque, severe shear and bending stress
- Custom traction tread available up to 7 inches deep

### Application



### Tire Features

ELLIPTICAL APERTURES*	CUT RESISTANT COMPOUND	PUNCTURE RESISTANT	WHEEL & DISK SYSTEM

\*only available with Solidflex tires

# Brawler HD Loader

PREMIUM OTR SOLID

## HD SOLIDFLEX SMOOTH

Tire Size	Pneumatic Equivalent Size	Overall Diameter [mm]	Section Width [mm]	Rubber Thickness [mm]	Tread Depth [mm]	Load Capacity 10 km/h [kg]
55x10x18	17.5-25	1,397	457	254	127	10,010
59x12x20.5	20.5-25	1,500	521	292	165	11,835
62x13x21	20.5-25	1,575	533	330	191	12,575
66x16x24	23.5-25	1,675	610	406	254	14,665
69x17x28	26.5-25	1,755	711	432	279	17,770
73x18x31	29.5-25	1,855	787	450	305	20,360
80x18x35	35/65-33	2,030	889	457	305	26,550

## HD SMOOTH

Tire Size	Pneumatic Equivalent Size	Overall Diameter [mm]	Section Width [mm]	Rubber Thickness [mm]	Tread Depth [mm]	Load Capacity 10 km/h [kg]
55x10x18	17.5-25	1,397	457	254	127	13,345
59x12x20.5	20.5-25	1,500	521	292	165	15,780
62x13x21	20.5-25	1,575	533	330	191	16,765
66x16x24	23.5-25	1,675	610	406	254	19,555
69x17x28	26.5-25	1,755	711	432	279	23,695
73x18x31	29.5-25	1,855	787	450	305	27,150
80x18x35	35/65-33	2,030	889	457	305	35,400



TRELLEBORG

Trelleborg Wheel Systems Italia S.p.A.  
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy  
Phone: +39 0774 384701 - Fax: +39 0774 384702  
[www.trelleborg.com/wheels](http://www.trelleborg.com/wheels)

[facebook.com/TrelleborgConstruction](https://facebook.com/TrelleborgConstruction)  
[youtube.com/TrelleborgConstruction](https://youtube.com/TrelleborgConstruction)



Download the App for free



Tire iBrochure