



PREMIUM MATERIALS HANDLING RESILIENT

PREMIA

Balanced Performance

Premia tires are designed for durable performance. The square footprint provides even wear and increased stability. The combination of advanced compounding and premium natural rubber combines to create a tire that has excellent heat resistance.

Premia is available in a wide range of sizes and special compounds. It's the reliable solution for all your materials handling needs.

PERFORMANCE DEFINED

ENERGY SAVING

Trelleborg is a **leading approved tire manufacturer to the OEMs**. We work closely with them to ensure we meet the requirements of energy consumption. This results in **reduced costs** for our customers.

COMFORT

Trelleborg understands the requirements of a **safe working environment**. Our products are designed to reduce vibration and **keep noise to a minimum level**. We follow the strictest regulations for work safety while providing a comfortable ride.

STABILITY

Trelleborg products are designed to have **large footprints**, maximizing the contact area leading to better stability and even tire wear.

TIRE LIFE

Trelleborg products guarantee **best in class** performance. This results in longer tire life, **additional hours of usage**, reduced downtime and lower maintenance costs.

PREMIUM MATERIALS HANDLING RESILIENT

PREMIA

Tire Size	Profile	Rim	Max Width (in)	Overall Diameter	Load Capacity 10 mph (lbs)	Load Capacity 6 mph (lbs)	Weight (lbs)
15x4.5-8	Premia Rib	3.00	4.5	15.0	1,450	2,000	23.8
15x4.5-8	Premia	3.00	4.5	15.0	1,450	2,000	37.0
5.00x8	Premia	3.00	4.8	17.8	1,935	2,670	37.0
16x6-8	Premia	4.33	5.9	16.2	2,300	3,170	37.0
18x7-8	Premia	4.33	5.7	18.0	2,700	3,750	45.4
6.00x9	Premia	4.33	5.6	20.8	3,065	4,230	58.6
21x8-9	Premia	4.00	7.4	20.3	4,480	6,190	75.4
140x55-9	Premia	6.00	5.1	15.0	1,830	2,530	22.7
200x50-10	Premia	4.00	7.6	18.0	3,770	5,200	54.7
6.50x10	Premia	6.50	6.5	22.5	4,210	5,810	79.8
23x9-10	Premia	5.00	8.2	22.9	5,450	7,525	107.6
23x10-12	Premia	6.50	9.1	22.8	6,385	8,820	110.0
27x10-12	Premia	8.0 0	9.1	26.6	7,730	10,680	162.0
7.00x12	Premia	5.00	6.6	25.9	4,810	6,640	103.2
7.00x15	Premia	5.50	7.3	28.5	5,725	7,905	130.1
28x9-15	Premia	7.00	8.1	27.6	6,520	9,000	131.4
8.25x15	Premia	6.50	8.0	32.0	7,875	10,875	200.6
250x15	Premia	7.00	8.3	28.1	6,960	9,615	146.4
250x15	Premia	7.50	8.3	28.1	7,460	10,300	148.2
300x15	Premia	8.00	9.5	32.0	9,550	13,190	233.7
32x12.1-15	Premia	9.75	11.8	32.2	11,405	15,745	291.9

SPECIAL COMPOUNDS AVAILABLE

Non-Marking

Note: Our compounding expertise allows us to offer a wide range of compounds. Please contact us for more details.

TREAD PATTERNS

Premia

Premia Rib



TRELLEBORG.COM/WHEELS