



Ecosolid

RESILIENT - LOW INTENSITY APPLICATIONS

Main Benefits

- **Deep tread design**
For enhanced tire life and heavy ground traction.
- **Enhanced stability**
Faster load positioning and cornering.
- **Energy efficiency**
Low rolling resistance for improved energy efficiency.

Polymer Engineering, Application Expertise

Trelleborg strives to deliver optimum performance for all our customers. We offer problem-solving products in our premium range. Contact our application specialists to learn more about our latest tire solutions.



STABILITY



TIRE LIFE



BATTERY LIFE



OVERHEATING TIRE



VIBRATION



TIRE CRACKING



EXPLOSION RISK



TIRE CHUNKING

Special compounds available





Size	Alternative Size	Rim	Tire type & Compound availability	Product Dimensions [mm]		Load Capacity [kg]		
			● STD ■ LOC ▼ BOTH	Overall Diameter	Section Width	Other	Counterbalanced Lift Trucks up to 25 km/h	
			Multi Purpose			Static	Load Wheel	Steering Wheel
15x4½-8	125/75-8	3.00D-8	▼	372	103	1,210	1,040	800
5.00-8		3.00D-8	▼	457	122	1,650	1,415	1,090
16x6-8	150/75-8	4.33R-8	▼	408	143	1,740	1,495	1,150
18x7-8	180/70-8	4.33R-8	▼	450	143	2,490	2,145	1,650
140/55-9	15x5.5-9	4.00E-9	▼	370	127	1,360	1,170	900
6.00-9		4.00E-9	▼	508	140	2,190	1,885	1,450
21x8-9	200/75-9	6.00E-9	▼	508	185	3,200	2,755	2,120
6.50-10		5.00F-10	▼	559	163	2,720	2,340	1,800
200/50-10		6.50F-10	▼	447	186	2,870	2,470	1,900
23x9-10	225/75-10	6.50F-10	▼	571	190	4,000	3,445	2,650
7.00-12		5.00S-12	▼	660	168	3,380	2,920	2,240
23x10-12	250/60-12	8.00G-12	▼	571	224	4,380	3,770	2,900
27x10-12	250/75-12	8.00G-12	▼	656	230	4,530	3,900	3,000
7.00-15		5.5-15	▼	711	178	4,115	3,545	2,725
8.25-15		6.5-15	▼	787	206	5,510	4,750	3,650
28x9-15	225/75-15 (8.15-15)	7.0-15	▼	686	204	4,000	3,445	2,650
250-15	250/70-15	7.0-15	▼	704	216	5,510	4,745	3,650
300-15	315/70-15	8.0-15	▼	812	254	6,795	5,850	4,500
355/65-15	32x12½-15(350-15)	9.75-15	▼	809	278	9,060	7,800	6,000



TRELLEBORG

Trelleborg Wheel Systems Italia S.p.A.
Via Nazionale Tiburtina, 143 - 00010 Villa Adriana (RM) Italy
Phone: +39 0774 384701 - Fax: +39 0774 384702
www.trelleborg.com/wheels



facebook.com/Trelleborgmaterialhandling

Download the App for free

