


Hydrokor VI In-Plant Coring Machine

The Hydrokor VI provides the highest reliability and performance.



With a 90 inch turntable and ability to core up to a 32 inch hole, this machine will provide many years of return on your investment.

For a more powerful 20 hp power unit, time saving auto feed and retract features, and a digital display of turntable position, you can purchase the Hydrokor VI with the upgrade option package.

Whichever Hydrokor machine you choose you can count on getting the best quality, reliability and customer service.

WITH UPGRADE OPTION PACKAGE

Heavy duty 20 hp hydraulic power unit that delivers 80 % more coring power to the drill for high volume production coring.

Auto feed and retract for fast, efficient, hands-off operation. Frees the operator to perform other tasks while machine is coring.

Digital display with new direct drive encoder system provides precise turntable position that can be reset to zero at any position.

Field configurable for 208, 230, or 460 volt service for maximum flexibility.

FEATURES OF THE BASIC MODEL

32 inch feed stroke.

90 inch powered turntable.

7 to 32 inch core drill capability.

2 speed Char-Lynn drill motor.

Rugged Gresen hydraulic control valves.

Left or right hand controls, field configurable.

Drill elevation from 6 to 49 inches.

4 inch tall turntable positioners allow structures to be lifted on and off with a forklift.

Independent turntable with quick disconnect hydraulic lines for coring larger structures.

Heavy duty 10 hp hydraulic power unit with heat exchanger for continuous operation.

Premium quality Barnes gear pump and Baldor motor.



TRELLEBORG

WWW.TRELLEBORG.COM/PIPE-SEALS