

# Rollin<sup>®</sup>Type150


## Key performance

- Consistent throw length, uniform nip pressure, easy washup
- The best adhesive in the market to avoid creeping and lifting
- Clean and easy removal from the cylinder
- Improved blanket lifetime

## MAIN APPLICATION

Business Forms, labels

**Rollin Type150 is available in multiple ply type and multiple thickness**



**Rollin Type150**



## The product at a glance

INK COMPATIBILITY	UV
PRINTING SURFACE COLOUR	Light Blue
THICKNESS (mm)	0,90-0,94; 0,98-1,00; 1,04-1,06
AVERAGE LOAD VALUE N/cm <sup>2</sup> @ 0,23 mm Indentation	Not Applicable
SURFACE ROUGHNESS (Ra micron)	1,7
ADDITIONAL INFORMATION	
BLANKET CONSTRUCTION	Adhesive

**FOR ANY FURTHER DETAILS AND FOR A QUOTATION  
PLEASE REFER TO YOUR SALES MANAGER  
OR EMAIL US AT: [printingsm@trelleborg.com](mailto:printingsm@trelleborg.com)**