


NPC - Corrugated Pipe Adapter



- Provides a good sealing surface on corrugated HDPE pipe
- Easy to install - Simply stretch it over the pipe to the desired location
- Certified to ASTM C923 when used with a Kor-N-Seal® Connector
- Specifically designed for use with most sizes of ADS, Hancor, Lane, N-Flow, Quality Culvert, JM Eagle and Contech A2000

The unique design of our Pipe Adapter distributes the force from the pipe clamp on our Kor-N-Seal connector directly against the inside walls of the pipe corrugations, creating a watertight seal up to 24 inches*.



Pipe Size	Pipe Mfg.	Pipe O.D. Ref. ± ¼	Adapter Part No.	Kor-N-Seal Connector	Sealing Capability
8	ADS	9 1/8	CGA-8A	S106-12 or S406-12	WT
	Hancor	9 1/8	CGA-8H		WT
	Lane	9 7/16	CGA-8L		ST
10	ADS	11 3/8	CGA-10A	S106-16A	WT
	Hancor	11 3/8	CGA-10H		WT
	Lane	11 3/4	CGA-10L		ST
12	ADS	14 3/8	CGA-12A	S106-16T or S106-20BWS	WT
	Hancor	14 3/8	CGA-12H		WT
	Lane	14 9/16	CGA-12L		ST
	JM Eagle	14 1/4	CGA-12JM	S106-20BWS	ST
	Quality Culvert	14 1/2	CGA-12Q		ST
	N-Flow	15	CGA-12N		ST
15	Contech A2000	12 3/4	CGA-12C	S106-16A	WT
	ADS	17 1/2	CGA-15A	S106-20WS	WT
	Hancor	17 1/2	CGA-15H		WT
	Lane	17 7/16	CGA-15L		ST
	N-Flow	18	CGA-15N	S206-22 or S206-24A	ST
	Quality Culvert	17 1/2	CGA-15Q	S106-20WS	ST
18	Contech A2000	15 5/8	CGA-15C	S106-20AWS	WT
	JM Eagle	17 1/2	CGA-15JM	S206-20L	ST
	ADS	21 3/16	CGA-18A	S206-24L, S306-24L	WT
	Hancor	21 3/16	CGA-18H		WT
	Lane	21 3/16	CGA-18L		ST
N-Flow	21	CGA-18N	ST		
Quality Culvert	21 5/16	CGA-18Q	ST		
21	Contech A2000	19 1/4	CGA-18C	S206-22L, S306-22L or S206-24A	WT
	JM Eagle	20 7/8	CGA-18JM	S206-24	WT
	Contech A2000	22 9/16	CGA-21C	S206-26, S306-26	WT
24	ADS	27 3/4	CGA-24A	S206-30L-32, S306-30L-32	WT
	Hancor	27 3/4	CGA-24H	S206-30L-32	WT
	Lane	28	CGA-24L	S206-32, S306-32	ST
	N-Flow	28	CGA-24N	S206-32, S306-32	ST
	Quality Culvert	27 15/16	CGA-24Q	S206-30L-32, S306-30L-32	ST
	Contech A2000	25 1/2	CGA-24C	S206-28L, S306-28L	WT
	JM Eagle	27 1/2	CGA-24JM	S206-30L	ST

Pipe Size	Pipe Mfg.	Pipe O.D. Ref. ± ¼	Adapter Part No.	Kor-N-Seal Connector	Sealing Capability
30	ADS	35	CGA-30A	S206-38L, S306-38L	ST
	Hancor	36	CGA-30H	S206-40, S306-40	ST
	Lane	34 3/4	CGA-30L	S206-38L, S306-38L	ST
	N-Flow	35	CGA-30N	S206-38L, S306-38L	ST
	Quality Culvert	34 7/8	CGA-30Q	S206-38, S306-38	ST
	Contech A2000	32 3/16	CGA-30C	S206-36, S306-36	ST
	JM Eagle	34 5/8	CGA-30JM	S206-38	ST
36	ADS	41 7/8	CGA-36A	S206-44L-46, S306-44L-46	ST
	Hancor	41 3/8	CGA-36H	S206-44L, S306-44L	ST
	Lane	40 7/8	CGA-36L	S206-44L, S306-44L	ST
	N-Flow	41 1/8	CGA-36N	S206-44L, S306-44L	ST
	Quality Culvert	41 3/8	CGA-36Q	S206-44L, S306-44L	ST
	Contech A2000	38 3/4	CGA-36C	S206-42L, S306-42L	ST
	JM Eagle	41 1/2	CGA-36JM	S206-44L	ST
42	ADS	47 11/16	CGA-42A	S206-52L	ST
	Hancor	47 15/16	CGA-42H		ST
	Lane	47 3/8	CGA-42L		ST
	N-Flow	48	CGA-42N		ST
	Quality Culvert	48 1/4	CGA-42Q		ST
	JM Eagle	47 3/8	CGA-42JM		S206-52
48	ADS	53 7/16	CGA-48A	S206-58L	ST
	Hancor	53 11/16	CGA-48H		ST
	Lane	54	CGA-48L		ST
	N-Flow	54	CGA-48N		ST
	Quality Culvert	54 3/4	CGA-48Q		ST
	JM Eagle	53 13/16	CGA-48JM		S206-58
54	Hancor	60 15/16	CGA-54H	S206-64L or S206-66	ST
60	ADS	66 1/4	CGA-60A	S206-70L	ST
	Hancor	67 3/16	CGA-60H	S206-72	ST
	N-Flow	67	CGA-60N		ST

WT = Watertight
ST = Soiltight