

Request for information **Marine Propulsion Application**

Customer Information

Date _____

Enquiry from	
Telephone N°	
Fax N°	
Email address	
End user	

Application Details

Vessel type	
Vertical shock criteria	
Lateral shock criteria	
Longitudinal shock criteria	
Minimum temperature @ mountings (°C)	
Maximum temperature @ mountings (°C)	
Environmental conditions	

Engine Details

Manufacturer						
Model						
Configuration	Vee		In-line		Boxer	
Weight (Kg)						
Idle speed (rpm)						
Max speed (rpm)						
Max Torque (Nm)						
Max Power (bhp)						
Datum position description						
Centre of gravity (C.O.G) position from datum (mm)	X		Y		Z	
Mass moments of inertia (Kg/mm ²)	Ixx		Iyy		Izz	
Block sizes (mm)	X		Y		Z	
Number of mount positions						

Transmission Details

Manufacturer										
Model										
Description	Standard	Offset	Down Angle	V Drive	Remote					
Weight (Kg)										
Mass Moment of Inertia (Kg/mm ²)	Ixx		Iyy		Izz					
Block sizes (mm)	X		Y		Z					
C.O.G position from datum (mm)	X		Y		Z					
Gear ratios										
Output shaft position & angle	X		Y		Z		Angle			
Number of mount positions										

Mount information

Mount number	Position from datum		
	X	Y	Z
1			
2			
3			
4			
5			
6			

Additional Information

Layout example

