


NPC – Vertakor® 1200

Portable Core Drilling Machine

Our Vertakor 1200 Series of Core Drilling Machines is ideal for on-site drilling of openings for use with Trelleborg NPC's Kor-N-Seal® Pipe-to-Manhole and Kor-N-Tee® Pipe-to-Pipe Connectors for fast, economical, watertight connections.

Complete Assemblies:

VERTAKOR 1200
Electric Start, Hydraulic Power Unit,
Flat Base, Core Diameter Range
7" to 16" (water tank included)



P/N 90262-H

*As above, but with a Pipe Base instead of a Flat Base,
P/N 91480-H*

Specifications for Complete Assembly Models: (P/N 90262-H & 91480-H)

Diameter Range: Up to 16 inches

Center Line of Core Drill: 14 inches minimum,
18 inches maximum from anchor

Hydraulic Power Supply: 4 cycle gasoline motor
with electric start, 10 gallon hydraulic reservoir

Water Service: 2.5 gallon water tank or 3/8 inch
city water line



Length, Width, Height: 54 x 36 x 28 inches

Weight: 375 lbs.

Other Available Models:



(Power Units Sold Separately)

VERTAKOR 1200HF
Hydraulic Powerhead/Flat Base, Water
Tank, Core Diameter Range 7" - 16"
P/N 90269



VERTAKOR 1200HP
Hydraulic Powerhead/Pipe Base, Water
Tank, Core Diameter Range 7" - 16"
P/N 90537

VERTAKOR 1200GF
Gasoline Powerhead/Flat Base, Water
Tank, Core Diameter Range 2" - 12"
P/N 90540



VERTAKOR 1200GP
Gasoline Powerhead/Pipe Base, Water
Tank, Core Diameter Range 2" to 12"
P/N 90541



Optional Equipment:

WATER TANK
P/N 90203