


ASPIVRAC S



CONSTRUCTION & ENVIRONMENT Abrasive bulk materials vacuum systems

Applications

Industrial vacuum cleaning equipment for recovery of industrial waste (crushed minerals, sand, building site rubble, dust, shavings, etc.). For fixed installations (centralized cleaning systems) or mobile installations (vacuum tankers).
Pneumatic suction or discharge of abrasive powder or granulated products (grains, cereals, cattle feed granules, etc.).

Advantages

- n Robust and easy to handle.
- n Excellent bending radius.
- n Can be manufactured with cuffed ends.
- n Good cover resistance to abrasion.

Technical description

Inner tube: wear resistant NR, black, smooth.
Reinforcement: synthetic textile cords with embedded steel helix.
Cover: weather resistant NR, black, corrugated.
Temperature range: - 30 °C to + 80 °C.
Electrical properties: conductive tube and cover, $R < 10^6 \Omega/m$.



ASPIVRAC S											01/02/2012		
ID mm	Wall thickness mm	OD mm	Working pressure bar	Bursting pressure bar	Max. vacuum bar	Bending radius mm	Weight kg/m	Length m	Article number	Stock (n) or min. order m			
50	± 1.5	8.0	± 1.0	66.0	± 2.0	1.5	4.5	0.8	100	1.91	10	0061603	40
											20	0061604	n
60	± 1.5	8.0	± 1.0	76.0	± 2.0	1.5	4.5	0.8	120	2.46	10	0122616	40
											20	0122624	40
70	± 1.5	8.0	± 1.0	86.0	± 2.0	1.5	4.5	0.8	140	2.81	10	0122651	40
											20	0122699	40
75	± 1.5	8.0	± 1.0	91.0	± 2.0	1.5	4.5	0.8	150	3.02	10	0061605	40
											20	0061606	n
80	± 1.5	8.0	± 1.0	96.0	± 2.0	1.5	4.5	0.8	160	3.16	10	0061607	n
											20	0061608	n
90	± 1.5	8.0	± 1.0	106.0	± 2.0	1.5	4.5	0.8	180	3.46	10	0061609	n
											20	0061610	n
100	± 1.5	8.0	± 1.0	116.0	± 2.0	1.5	4.5	0.8	200	3.8	10	0061611	n
											20	0061612	n
110	± 1.5	8.0	± 1.0	126.0	± 2.0	1.5	4.5	0.8	220	4.15	10	0061613	40
											20	0061614	n
125	± 1.5	9.0	± 1.0	143.0	± 2.0	1.5	4.5	0.8	250	5.28	10	0061615	n
											20	0061616	n
150	± 1.5	8.5	± 1.0	167.0	± 2.0	1.5	4.5	0.8	300	6.26	10	0061617	n
											20	0061618	n
200	± 1.5	13.0	± 1.5	226.0	± 2.5	1.5	4.5	0.8	400	8.92	10	0061619	n

Branding
No branding

