

TrellTent® 3/2

- Flexible, durable and easy to handle



The original TrellTent® was developed in cooperation with the Medical Board of the Swedish Armed Forces, for field hospital use. It can also be used in for example rescue service and command centre applications. The tent is inflatable and can be ready for use in five minutes.



Simplicity makes a difference: TrellTent® 3/2 is a tent with inflatable beams, that provides short erection time (down to 5 minutes), low storage volume and a tent that is easy to handle. An inflated tent can be left for weeks without maintenance.

Designed for flexibility and stability: TrellTent® 3/2 has 3 sections and 2 doors. For a clean internal environment and easy handling, it is provided with a fixed floor (area 37 m²). It is part of a modular inflatable tent system with a great variety of tent sizes and is easily connected to other tents by means of a connection system around the doors. The fixed beams with separate inner tubes provide high air tightness and excellent stability. The half-cylindrical shape of the tent adds to the stability of the construction.

Made to be durable: The high quality of materials and craftsmanship gives a tent with excellent wear and tear properties and a long life span.

Accessories: A variety of accessories are available such as black-out section, connection sections, separate inner ground sheets, inner linings, sun screens, NBC covers and air distribution channels.

TECHNICAL DATA:

MATERIAL:	PVC-COATED POLYESTER FABRIC, 755 G/M ²
COLOUR, OUTSIDE:	YELLOW
COLOUR, INSIDE:	LIGHT GREEN
DIMENSIONS:	L=7.25 M; W=5.2 M
HEIGHT:	2.6 M (TO TENT FABRIC)
AREA:	37 M ²
VOLUME:	75 M ³
VOLUME, PACKED:	APPROX. 1.0 M ³
WEIGHT:	APPROX. 195 KG
NUMBER OF DOORS:	2 PCS
NUMBER OF WINDOWS:	4 PCS
NUMBER OF BEAMS:	4 PCS
AIR PRESSURE, BEAMS:	18 kPa
ZIPPER:	METAL
ACCESSORIES INCLUDED:	TARPAULIN, SPACING COLLARS IN BAG, VALVE SPANNER, MANUAL

