

BERGALAV

AGRI & FOOD

Cleaning in food environment



Applications

Cleaning hoses with hot water and steam up to + 160 °C in food processing plants.

Suitable for liquid foodstuff, wine, milk, beer, water, soda.

Advantages

- Highly flexible.
- Specially adapted to keep round on reels.
- Contains no phthalate.

Technical description

Inner tube: food grade quality EPDM, white, smooth.

Reinforcement: synthetic textile.

Cover: weather resistant EPDM, blue, smooth.

Temperature range: - 30 °C to + 160 °C.

Standard/Approval:

EU regulation n° 1935/2004.

FDA regulation 21 CFR 177.2600.

French legislation.

All relevant migrations tests (France and FDA) were performed and confirmed compliant by the French institute of Poitiers (IANESCO).

Couplings/Fittings

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

BERGALAV

20/05/2010

ID		OD		Working pressure	Bursting pressure	Bending radius	Weight	Length	Article number	Stock (■) or min. order
mm		mm		bar	bar	mm	kg/m	m		m
10.0	± 0.6	18.0	± 0.7	10	30	75	0.25	20	5501308	◇
								40	5501309	■
13.0	± 0.6	22.0	± 0.7	10	30	95	0.35	20	5500857	■
								40	5500858	■
16.0	± 0.7	25.0	± 0.8	10	30	110	0.41	20	5500859	■
								40	5500860	■
19.0	± 0.8	29.0	± 0.9	10	30	135	0.54	20	5500861	■
								40	5500862	■
25.0	± 1.0	36.0	± 1.0	10	30	180	0.74	20	5500863	■
								40	5500564	■

Branding

◇ upon availability



and embossed: week/year

