

SUPERVRAC



CONSTRUCTION & ENVIRONMENT
Bulk tank truck discharge

Applications

Pneumatic transport of bulk abrasive products.
Discharge from road and rail tankers and delivery to storage bins (cement, sand, limestone, coal, etc.).

Advantages

- n Light weight, flexible hose that coils flat.
- n Excellent resistance to abrasion.
- n Static conductive tube.

Technical description

Inner tube: wear resistant NR, black, smooth.
Reinforcement: synthetic textile.
Cover: weather resistant NR, black, fabric impression.
Temperature range: - 30 °C to + 90 °C.
Electrical properties: conductive tube and cover, $R < 10^6 \Omega/m$.



SUPERVRAC											01/02/2012
ID mm	Wall thickness mm		OD mm	Working pressure bar	Bursting pressure bar	Weight kg/m	Length m	Article number	Stock (n) or min. order m		
75	6.75	± 1.25	88.5	± 2.0	7.0	21	1.83	20	0060675	120	
								40	0060674	120	
	9.00	± 1.00	93.0	± 1.5		2.75	20	0060189	∞		
85	6.00	± 1.00	97.0	± 1.5	7.0	21	2.03	40	0060193	n	
								20	0129699	120	
89	6.25	± 1.25	101.5	± 2.0	7.0	21	2.07	40	0129700	120	
								20	0060682	n	
100	6.00	± 1.00	112.0	± 1.5	7.0	21	2.4	40	0060683	n	
								20	0129701	120	
	9.00	± 1.00	118.0	± 1.5		3.58	20	0129702	120		
110	6.50	± 1.25	123.0	± 2.0	7.0	21	2.71	40	0060194	n	
								20	0060195	n	
	40	0060684	n								
127	8.50	± 1.25	144.0	± 2.0	7.0	21	4.2	40	5006696	200	
								20	0060685	120	
152	8.50	± 1.25	169.0	± 2.0	7.0	21	5.0	40	0060686	120	
								20	0060689	120	
								40	0060690	120	

∞ Upon availability.

Branding

