

SUPERVRAC TAN

CONSTRUCTION & ENVIRONMENT
Evacuation and material handling hoses



Applications

Pneumatic transport of bulk abrasive products.
Discharge from road and rail tankers, and delivery to storage bins: cement, sand, lime and also cereals, fertilizers, cattle feed and chemicals (PVC, dye stuffs, granulates, etc.).

Advantages

- n Light weight, flexible hose that coils flat.
- n Excellent resistance to abrasion.

Technical description

Inner tube: heavy duty abrasion resistant NR, tan, smooth.
Reinforcement: synthetic textile.
Cover: weather resistant NR, black, fabric impression.
Temperature range: - 30 °C to + 70 °C.
Electrical properties: non conductive tube with built-in wire.

SUPERVRAC TAN

26/09/2011

ID mm	Wall thickness mm	OD mm	Working pressure bar	Bursting pressure bar	Weight kg/m	Length m	Article number	Stock (n) or min. order m
75	6.0 ± 1.25	87.0 ± 1.5	7.0	21	1.72	20	0070661	120
						40	0125111	120
85	6.0 ± 1.25	97.0 ± 1.5	7.0	21	1.81	20	0070662	80
						40	0070663	80
89	6.0 ± 1.25	101.0 ± 1.5	7.0	21	1.98	20	0060614	n
						40	0060615	n
100	6.0 ± 1.25	112.0 ± 1.2	7.0	21	2.24	20	0070664	120
						40	0070665	120
110	6.5 ± 1.25	123.0 ± 1.5	7.0	21	2.5	20	0060617	n
						40	0060618	n

Branding

