

**CLOSED CELL EPDM SPONGE****RM200338**

<b>Properties of ASTM D-1056: 2A2/2A3</b>	<b>Required Value</b>	<b>Typical Value</b>	<b>ASTM Test Method</b>
Compression-deflection, 25% deflection limits, psi	5 to 13	9.25	D 1056
Compression-deflection, 168 Hrs @ 70 C, % Chg, Max	+/- 30	20.8	D 1056
Compression set, 22 h @ Rm. Temp. Suffix B, % set max	25	15	D 1056
Water absorption, max. % weight	5	1.1	D 1056