

# TRELLBLAST S



CONSTRUCTION & ENVIRONMENT  
Blasting and guniting

## Applications

For cleaning and shot blasting castings, metal, stone, and concrete surfaces.

## Advantages

- Light weight and flexible for easy handling.
- Conductive inner tube compound gives increased safety for the operator, since there is no risk of wire breakage in use.

## Technical description

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile.

Cover: wear and weather resistant SBR, black, fabric impression.

Temperature range: - 30 °C to + 70 °C.

Electrical properties: conductive tube,  $R < 2 \cdot 10^6 \Omega/m$ .

Special properties: abrasion resistance of tube  $< 70 \text{ mm}^3$  according to DIN 53516

# TRELLBLAST S

29/07/2011

ID mm	Wall thickness mm	OD mm	Working pressure bar	Bursting pressure bar	Bending radius mm	Weight kg/m	Length m	Article number	Stock (n) or min. order m
13	7.0 ± 0.5	27.0 ± 1	10.0	30	65	0.56	40	5026067	n
16	7.0 ± 0.5	30.0 ± 1	10.0	30	80	0.68	40	5026068	400
19	7.5 ± 0.5	34.0 ± 1	10.0	30	100	0.74	40	5501321	n
25	7.0 ± 0.5	39.0 ± 1	10.0	30	125	0.86	40	5501322	n
32	8.0 ± 0.5	48.0 ± 1	10.0	30	160	1.3	40	5501323	n

Branding



**TRELLEBORG**  
ENGINEERED SYSTEMS

Trelleborg Industrie SAS - ZI La Combaude - Rue de Chantemerle - 63050 Clermont-Ferrand Cedex 2 - France  
[www.trelleborg.com/industrialhose](http://www.trelleborg.com/industrialhose)