

# TRELLOIL S



## CHEMICAL PETROCHEMICAL

Oil and petroleum/Tank truck suction and discharge

### Applications

Suction and discharge of petroleum products with aromatic content up to 50 % in all industrial applications.  
Road tanker equipment for oil and petrol deliveries.

### Advantages

- n Easily cut to length and fitted with couplings.
- n Light weight and flexible, even at cold temperature.
- n Dissipation of static electricity ensured by contact of built-in wire with the coupling.

### Technical description

Inner tube: oil and petrol resistant NBR, black, smooth.  
Reinforcement: synthetic textile with embedded steel helix.  
Cover: oil and weather resistant NBR/SBR, black, fabric impression.  
Temperature range: - 30 °C to + 80 °C.  
Electrical properties: built-in conductive wire

## TRELLOIL S

14/12/2011

ID mm	Wall thickness mm	OD mm	Working pressure bar	Bursting pressure bar	Max. vacuum bar	Bending radius mm	Weight kg/m	Length m	Article number	Stock (n) or min. order m
25	5.25 ± 0.5	35.5 ± 1.0	10.0	30	0.9	50	0.84	20	5501411	200
								40	5501412	200
32	5.25 ± 0.5	42.5 ± 1.0	10.0	30	0.9	65	0.99	20	5501413	n
								40	5501414	n
35	5.75 ± 0.5	45.5 ± 1.0	10.0	30	0.9	70	1.06	20	5501489	200
								40	5501490	200
38	5.75 ± 0.5	49.5 ± 1.0	10.0	30	0.9	80	1.22	20	5501415	n
								40	5501416	n
40	5.75 ± 0.5	51.5 ± 1.0	10.0	30	0.9	85	1.27	20	5501491	n
								40	5501492	n
45	6.00 ± 0.5	57.0 ± 1.0	10.0	30	0.9	90	1.49	20	5501493	120
								40	5501494	120
50	6.50 ± 0.75	63.0 ± 1.0	10.0	30	0.9	125	1.81	20	5501417	n
								40	5501418	n
55	6.50 ± 0.75	68.0 ± 1.5	10.0	30	0.9	145	1.95	20	5501495	120
								40	5501496	120
60	6.50 ± 0.75	73.0 ± 1.5	10.0	30	0.9	150	2.21	20	5501419	n
								40	5501420	n
63	6.50 ± 0.75	76.0 ± 1.5	10.0	30	0.9	160	2.24	20	5501421	120
								40	5501422	120
70	7.50 ± 0.75	80.0 ± 1.5	10.0	30	0.9	210	2.86	20	5501497	120
								40	5501498	120
75	7.50 ± 0.75	90.0 ± 1.5	10.0	30	0.9	225	3.03	20	5501423	120
								40	5501424	120
80	7.50 ± 0.75	95.0 ± 1.5	10.0	30	0.9	280	3.21	20	5501425	n
								40	5501426	n
89	7.50 ± 0.75	104.0 ± 1.5	10.0	30	0.9	335	3.55	20	5501499	80
								40	5501500	80
100	7.50 ± 0.75	115.0 ± 1.5	10.0	30	0.9	400	3.94	20	5501427	80
								40	5501428	80

### Branding

