

TRELLVAC Handler TAN



CONSTRUCTION & ENVIRONMENT

Industrial vacuum bulk products

Applications

Extraction and transport hose for abrasive materials such as sand, gravel, stone, sludge, etc.

Advantages

- Tan tube non staining.
- Both for vacuum and discharge.
- Conductive hose with built-in wire.
- Good wear resistant tube.
- Could be produced with cuffed-ends.

Resistance ○○○○○

Flexibility ○○○

Weight ○○

Technical description

Inner tube: wear resistant NR, tan, smooth.

Reinforcement: synthetic textile with embedded steel helix.

Cover: wear and weather resistant NR, black, corrugated.

Temperature range: - 30 °C to + 90 °C.

Electrical properties: R < 10⁶ Ω/m, built in conductive wire.

Complementary information

Cuffed-end upon request. Min. of order: 20 m.

Could be produced with white food grade NR inner tube. Min. of order: 20 m.

TRELLVAC Handler TAN

27/04/2007

ID	OD *		Cuff		Working pressure	Bursting pressure	Max. vacuum	Bending radius	Weight	Lenght	Stock (■) or min. order
	mm	mm	OD	Lenght							
60.0	± 1.0	77.0 ± 1.5	80	70	3	9	0.9	240	1.9	2 to 10	20
65.0	± 1.0	82.0 ± 1.5	85	75	3	9	0.9	260	2.1	2 to 10	20
80.0	± 1.0	99.0 ± 1.5	100	90	3	9	0.9	320	2.7	2 to 10	20
90.0	± 1.0	109.0 ± 1.5	113	110	3	9	0.9	360	3.1	2 to 10	20
100.0	± 1.0	119.0 ± 1.5	123	110	2.5	7.5	0.9	400	3.4	2 to 10	20
110.0	± 1.0	129.0 ± 1.5	133	110	2	6	0.9	550	3.7	2 to 10	20
120.0	± 1.0	139.0 ± 1.5	143	120	2	6	0.9	600	4.0	2 to 10	20
125.0	± 1.0	145.0 ± 1.5	147	125	2	6	0.9	750	4.3	2 to 10	20
130.0	± 1.0	153.0 ± 1.5	154	130	2	6	0.9	780	5.5	2 to 10	20
150.0	± 1.0	170.0 ± 1.5	175	150	2	6	0.9	900	5.5	2 to 10	20
200.0	± 1.0	230.0 ± 1.5	231	200	0.5	2	0.9	1200	12.2	2 to 10	20

* OD measured on top of corrugation

Branding

