

BERGALAV

AGRI & FOOD

Cleaning in food environment



Applications

Cleaning hoses with hot water and steam up to + 160 °C in food processing plants.
Suitable for liquid foodstuff, wine, milk, beer, water, soda.

Advantages

- n Highly flexible.
- n Specially adapted to keep round on reels.
- n Contains no phthalate.

Technical description

Inner tube: food grade quality EPDM, white, smooth.
Reinforcement: synthetic textile.
Cover: weather resistant EPDM, blue, smooth.
Temperature range: - 30 °C to + 160 °C.
Standard/Approval: EU regulations n° 1935/2004 and 2023/2006.
FDA regulation 21 CFR 177.2600.
French legislation.
All relevant migrations tests (France and FDA) were performed and confirmed compliant by the French institute of Poitiers (IANESCO).

Couplings/Fittings

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

BERGALAV

10/05/2011

| ID mm | OD mm | Working pressure bar | Bursting pressure bar | Bending radius mm | Weight kg/m | Length m | Article number | Stock (■) or min. order m | | |
|----------|----------|----------------------------|-----------------------------|----------------------|----------------|-------------|----------------|---------------------------------|---------|---|
| 10 | ± 0.6 | 18.0 | ± 0.7 | 10.0 | 30 | 75 | 0.25 | 20 | 5501308 | □ |
| | | | | | | | | 40 | 5501309 | ■ |
| 13 | ± 0.6 | 22.0 | ± 0.7 | 10.0 | 30 | 95 | 0.35 | 20 | 5500857 | ■ |
| | | | | | | | | 40 | 5500858 | ■ |
| 16 | ± 0.7 | 25.0 | ± 0.8 | 10.0 | 30 | 110 | 0.41 | 20 | 5500859 | ■ |
| | | | | | | | | 40 | 5500860 | ■ |
| 19 | ± 0.8 | 29.0 | ± 0.9 | 10.0 | 30 | 135 | 0.54 | 20 | 5500861 | ■ |
| | | | | | | | | 40 | 5500862 | ■ |
| 25 | ± 1.0 | 36.0 | ± 1.0 | 10.0 | 30 | 180 | 0.74 | 20 | 5500863 | ■ |
| | | | | | | | | 40 | 5500864 | ■ |

□ Upon availability.

Branding



and embossed: week/year

