



T-900
TOTAL SOLUTION

PNEUMATIC TIRES



The Trelleborg pneumatic tire range has been developed for heavy duty use on forklift trucks and other industrial vehicles. This line of tires offer customers an additional range of tires besides solid rubber products. All the tires have a lug type tread pattern which provides optimal grip and traction in every condition. The cross-ply or diagonal structure further insures high stability and maximum safety. The casing is of high tensile strength cord which offers good resistance to fatigue and improves comfort.

- **NATURAL RUBBER**
- **GOOD RESISTANCE TO FATIGUE**
- **HIGH STABILITY
MAXIMUM SAFETY**
- **OPTIMAL GRIP
AND TRACTION**



TRELLEBORG T-900

- **DESIGNED FOR HEAVY DUTY USE IN ALL APPLICATIONS**
- **PREMIUM TREAD COMPOUND FOR MAXIMUM TIRE LIFE AND WEAR RESISTANCE**
- **EXTRA WIDE TREAD FOR INCREASED STABILITY AND TRACTION**
- **REINFORCED SIDE WALL FOR IMPROVED PROTECTION AGAINST SIDE IMPACTS**
- **REINFORCED BEAD AREA THAT PROTECTS THE WHEEL FLANGES**
- **EXCELLENT RIDE QUALITY**



T-900

Size	P.R.	Recommended rim	Inflated dimensions (mm)		Inflation pressure (±15%)		Weight Tire (kg)	Load capacity forklift up to 25 km/h (kg)	
			Width	O.D.	PSI	Bar		Front	Rear
5.00-8	10	3.00	140	468	145	10,00	6,9	1.415	1.090
18x7-8	16	4.33	168	462	145	10,00	10,0	2.145	1.650
6.00-9	12	4.00	160	543	145	10,00	10,9	1.885	1.450
6.50-10	12	5.00	182	590	130	9,00	14,0	2.145	1.650
23x9-10	20	6.50	230	585	145	10,00	25,5	3.445	2.650
7.00-12	14	5.00	191	680	131	9,00	18,9	2.755	2.120
	16	5.00	191	680	145	10,00	19,0	2.910	2.240
23x10-12	20	8.00	250	600	145	10,00	26,7	3.770	2.900
27x10-12	16	8.00	250	685	116	8,00	28,7	3.900	3.000
	24	8.00	250	685	145	10,00	31,8	5.040	3.875
7.00-15	14	5.50	200	756	127	8,75	24,3	3.275	2.520
7.50-15	16	6.00	215	785	145	10,00	31,3	3.900	3.000
28x9-15 (8.15-15)	14	7.00	230	710	145	10,00	26,2	3.900	3.000
8.25-15	14	6.50	247	841	116	8,00	36,9	4.225	3.250
250-15	20	7.50	240	742	145	10,00	36,1	5.040	3.875
300-15	20	8.00	290	840	130	9,00	47,9	6.500	5.000
7.50-16	12	6.00	215	805	116	8,00	30,1	3.630	2.790
9.00-20	14	7.00	265	1.015	130	9,00	62,9	5.850	4.500
10.00-20	16	7.50	294	1.080	130	9,00	75,2	6.500	5.000
11.00-20	18	8.00	305	1.110	145	10,00	86,0	7.800	6.000
12.00-20	20	8.50	325	1.145	145	10,00	101,3	8.970	6.900
	24	8.50	325	1.145	145	10,00	104,7	9.710	7.470
12.00-24	20	8.50	320	1.245	145	10,00	120,5	9.750	7.500
	24	8.50	322	1.249	145	10,00	120,5	9.945	7.650
14.00-24	24	10.00	380	1.360	145	10,00	160,0	12.350	9.500
	28	10.00	392	1.361	145	10,00	160,0	12.600	9.690

1) The above load capacities are based on available E.T.R.T.O and T.R.A. specifications for load and steering wheels on counterbalanced forklift trucks.

2) The Trelleborg pneumatic tires are available as complete sets (tire/tube/flap) or as tire & flap only.