


PARATUB

CHEMICAL PETROCHEMICAL
Chemical and corrosive products/Transfer



Applications

Discharge under pressure or gravity flow of corrosive products such as acids and alkalis.

Advantages

- This tube can be cut to length as required.
- Flexible and easy to handle.
- Excellent resistance to low temperatures.

Technical description

Inner tube: chemical resistant NR, beige, smooth.
Cover: fabric impression.
Temperature range: - 40 °C to + 70 °C .
Electrical properties: non conductive

PARATUB

13/04/2011

ID mm	Wall thickness mm	OD mm	Working pressure bar	Weight kg/m	Length m	Article number	Stock (■) or min. order m	
15.0	-0/+ 1	5.0	25.0 ±1	1	0.34	20	0200837	80
20.0	-0/+ 1	5.0	30.0 ±1	1	0.43	20	0200840	■
					0.43	40	0200841	200
25.0	-0/+ 1	5.0	35.0 ±1	1	0.51	20	0200843	■
					0.51	40	0200844	200
30.0	-0/+ 1	5.0	40.0 ±1	1	0.59	20	0200846	■
					0.59	40	0200847	200
35.0	-0/+ 1	5.0	45.0 ±1	1	0.67	20	0200849	■
					0.67	40	0200850	200
40.0	-0/+ 1	5.0	50.0 ±1	1	0.76	20	0200852	■
					0.76	40	0200853	200
50.0	-0/+ 1	5.0	60.0 ±1	1	0.92	20	0200855	■
					0.92	40	0200856	200
60.0	-0/+ 1	5.0	70.0 ±1	1	1.09	20	0200858	■
					1.09	40	0200874	120
80.0	-0/+ 1	7.5	95.0 ±1	1	2.12	20	0200876	■
					2.12	40	0200877	120

Branding

No branding.

