

PROJECTOR 100



CONSTRUCTION & ENVIRONMENT
Evacuation and material handling hoses

Applications

For spraying of wet mortar, mixed concrete, and other wet products.
Used as a service hose between pump and nozzle in transporting plaster, grout, and ready mixed concrete.

Advantages

- n High working pressure.
- n Light weight, flexible and easy to handle.
- n Abrasion resistant tube.

Technical description

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile.

Cover: wear and weather resistant SBR, black, fabric impression.

Temperature range: - 30 °C to + 70 °C.

Electrical properties: conductive tube, $R < 2 \cdot 10^6 \Omega/m$.

Special properties: abrasion resistance of tube $< 70 \text{ mm}^3$ according to DIN 53 516.

Complementary information

13.3 m lengths available on request, min. order is three pieces and by multiple of three.

Other wall thickness and/or bursting pressure on request.

PROJECTOR 100

05/01/2012

ID mm	Wall thickness mm	OD mm	Working pressure bar	Bursting pressure bar	Bending radius mm	Weight kg/m	Length m	Article number	Stock (n) or min. order m
25	7.0 +0/-1	39.0 ±1.0	40.0	100	100	0.87	40	0061494	n
32	8.0 +0/-1	48.0 ±1.0	40.0	100	150	1.24	40	0127153	400
35	6.5 +0/-1	48.0 +0/-1	40.0	100	180	1.06	40	0061496	n
38	10.0 +0/-1	58.0 ±1.0	40.0	100	180	1.84	40	0127156	200
40	10.0 +0/-1	60.0 ±1.0	40.0	100	200	1.92	40	0127170	200
50	7.5 ±0.7	65.0 ±1.5	40.0	100	370	1.64	40	0127179	400
	9.0 ±0.7	68.0 ±1.5				2.04	40	0061501	n
60	10.0 ±0.7	80.0 ±1.5	40.0	100	340	2.72	40	0127183	160
65	10.0 ±0.7	85.0 ±1.5	40.0	100	380	2.93	40	0061500	n

Branding



ENGINEERED SYSTEMS

Trelleborg Industrie SAS - ZI La Combaude - Rue de Chantemerle - 63050 Clermont-Ferrand Cedex 2 - France
www.trelleborg.com/industrialhose