



# EMR 1025 Earthmover Radial Tires

## PREMIUM RADIAL PNEUMATIC


Protecting people protecting assets, Trelleborg's EMR 1025 all-season tire adds extra comfort and safety on ice and snow.

EMR 1025 offers both the comfort and robustness of the EMR range and delivers high performance year round as a commercial all-season tire. Seasonal changeovers are no longer necessary.

### Main benefits

- Excellent damage protection and durability
- Perfect control and grip on ice and snow
- Maximum productivity for all-seasons
- Robust carcass to support eventual retreading\*

### Application



### Tire features




\*Carcass should be checked by a professional technician before retreading is permitted

# EMR 1025

PREMIUM RADIAL PNEUMATIC

## New sidewall protection



**Superior tire technology for year round use.**

## TECHNICAL DATA – LOADER SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth [mm]	Service Description LI/SS Loader	Tire Load Capacity (kg) 10 (km/h)	Tire Pressure (bar)
<b>17.5 R 25</b>	L2	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	28	* 176 A2	7,100	4.50
<b>20.5 R 25</b>	L2	17.00/2.0-25 (17.00/1.7-25)	31	* 186 A2	9,500	4.50
<b>23.5 R 25</b>	L2	19.50/2.5-25	34	* 195 A2	12,150	4.50

\*/\*\* - Index of tire strength

## TECHNICAL DATA – GRADER SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth [mm]	Service Description LI/SS Grader	Tire Load Capacity (kg) 40 (km/h)	Tire Pressure (bar)
<b>14.00 R 24</b>	G2	8.00TG-24 (SDC) 10.00VA-24 (SDC)	24	* 153 A8	3,650	3.75
<b>17.5 R 25</b>	G2	14.00/1.5-25 (14.00/1.5x25 DC, 14.00/1.3x25 DC)	28	* 153 A8	3,650	3.00
<b>20.5 R 25</b>	G2	17.00/2.0-25 (17.00/1.7-25)	31	* 161 A8	4,625	3.00
<b>23.5 R 25</b>	G2	19.50/2.5-25	34	* 170 A8	6,000	3.00

\*/\*\* - Index of tire strength



Follow us



Yokohama TWS S.p.A.  
Via Nazionale Tiburtina, 143 - 00019 Villa Adriana - Tivoli (RM), Italy  
Phone: +39 0774 3841 – info.tws@yokohama-tws.com  
www.trelleborg-tires.com

