

TRELLFLEX CHEM PTFE XX



CHEMICAL PETROCHEMICAL

Very aggressive chemicals

Applications

Very aggressive chemicals.

Technical description

Inner tube: film PTFE.

Reinforcement: polypropylene layers between two stainless steel helix.

Cover: PVC coated fabric, grey, corrugated.

Temperature: - 40 °C to + 100 °C.

Electrical properties: electrical conductivity ensured by the external helix in contact with fittings, $R < 10^6 \Omega$.

Standard/Approval: BS 5842.

TRELLFLEX CHEM PTFE XX

23/02/2010

ID		OD		Working pressure	Bursting pressure	Max vacuum	Bending radius	Weight	Length
inch	mm	inch	mm						
1"	25	1"29/64	37	14	56	0.9	100	0.98	30
1"1/4	32	1"11/16	43	14	56	0.9	120	1.20	30
1"1/2	38	1"3/64	52	14	56	0.9	140	1.56	30
2"	51	2"7/16	62	14	56	0.9	180	2.05	30
2"1/2	63	2"3/32	78.5	14	56	0.9	200	2.91	30
3"	76	3"3/4	95	14	56	0.9	280	3.35	30
4"	102	4"21/32	118	14	56	0.9	400	5.35	20

Branding:

