



EMR 1045 Earthmover Radial Tires

PREMIUM RADIAL PNEUMATIC

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability while the multi surface tread design delivers control and perfect grip when it's needed the most, whether on sand, rock, gravel or soil.

The strong radial carcass and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption.

Designed for rigid dumper applications, our EMR 1045 tire is the best choice for haulage operations in open pits and quarries.


Main Benefits

- · Supreme traction and stability
- · Excellent tire life due to deep tread
- · Reduced fuel consumption

Applications



Tire Features



PREMIUM RADIAL PNEUMATIC

TRANSPORT SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (mm)	Service Description LI/SS Transport	Tire Load Capacity (kg) at 50 (Km/h)	Tire Pressure (bar)
18.00 R 33	E4	13.00/2.5-33	54	** 191 B	10,900	6.50

*/** - Index of tire strength













