



TR-900

RADIAL PNEUMATIC - MAXIMUM INTENSITY APPLICATIONS

Main Benefits

- **Block tread design**
Large footprint lowers stress and maximizes tire life.
- **Radial technology**
For high speed, long distance applications.
- **Sidewall protection**
Reinforced sidewall to avoid impact damage.
- **Energy efficiency**
Low rolling resistance for improved energy efficiency.
- **Wear resistant technology**
Maximum lifetime, reduced downtime, increasing value.
- **Shock absorbance**
Tire absorbs shock from obstacles.
- **Rim security**
Rim protection from accidental damage and anti slip bead wires.
- **Enhanced stability**
Faster load positioning and cornering.
- **Explosion protection**
Anti Static, to reduce risk of sparks in potentially explosive atmospheres.

Polymer Engineering, Application Expertise

As part of our premium range this product is capable of performing in demanding applications to deliver high performance in key areas.



TIRE LIFE



PUNCTURE RESISTANCE



COOL RUNNING



STABILITY

TR-900

RADIAL PNEUMATIC - MAXIMUM INTENSITY APPLICATIONS

TREAD PATTERNS



TR-900

Size	Alternative Size	Rim	Product Dimensions [mm]			Minimal Dual Spacing [mm]	Inflation Pressure [bar]	Tire Type	Load Index	Speed Symbol	Load Capacity [kg]	
			Overall Diameter	Section Width	Tread Depth						Counterbalanced Lift Trucks up to 25 km/h	
											Load Wheel	Steering Wheel
5.00R8		3.00D-8	468	137	25	158	10.00	Tube Type	111	A5	1,415	1,090
6.00R9		4.00E-9	540	162	25	192	10.00	Tube Type	121	A5	1,885	1,450
6.50R10		5.00F-10	585	180	27	212	10.00	Tube Type	128	A5	2,340	1,800
7.00R12		5.00S-12	670	190	28	230	10.00	Tube Type	136	A5	2,915	2,240
28x9R15	225/75R15 (8.15R15)	7.0-15	706	230	25	248	10.00	Tube Type	149	A5	4,225	3,250
7.00R15	29x8R15	5.5-15	736	195	28	236	10.00	Tube Type	143	A5	3,540	2,725
250R15	250/70R15	7.0-15	736	252	27	282	10.00	Tube Type	153	A5	4,745	3,650
300R15	315/70R15	8.0-15	835	312	36	345	10.00	Tube Type	165	A5	6,695	5,150
8.25R15		6.5-15	838	232	32	281	10.00	Tube Type	153	A5	4,745	3,650
10.00R20	290/95R20	7.5-20	1,062	294	35	334	10.00	Tube Type	166	A5	6,890	5,300
12.00R20	330/95R20	8.5-20	1,136	320	41	378	10.00	Tube Type	176	A5	9,230	7,100
12.00R24	330/95R24	8.5-24	1,232	322	39	378	10.00	Tube Type	178	A5	9,750	7,500
14.00R24	385/95R24	10.0-24	1,416	390	64	450	10.00	Tube Type	193	A5	14,950	11,500



Follow us



Yokohama TWS S.p.A.
Via Nazionale Tiburtina, 143 - 00019 Villa Adriana - Tivoli (RM), Italy
Phone: +39 0774 3841 – info.tws@yokohama-tws.com
www.trelleborg-tires.com

