

VENDANGE

AGRI & FOOD
Foodstuff transfer



Applications

Specially designed for transfer of fresh grapes in wine processing industries.

Advantages

- Outstanding flexibility and easy handling.
- Weak tractive effort thanks to slicking cover.
- Smooth, seamless, white tube, that does not propagate bacterial growth.
- Resistant to cleaning with detergent or steam at temperatures up to 110 °C (during 10 minutes max).
- Non marking cover.
- Contains no phthalate.

Technical description

Inner tube: food grade quality NR, white, smooth.

Reinforcement: synthetic textile with embedded steel helix.

Cover: special polymer-based, red.

Temperature range: - 30 °C to + 80 °C.

Standard/Approval:

FDA regulation 21 CFR 177.2600.

French legislation.

All relevant migrations tests (France and FDA) were performed and confirmed compliant by the French institute of Poitiers (IANESCO).

Couplings/Fittings

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

VENDANGE

10/01/2012

ID mm		OD mm		Working pressure bar	Bursting pressure bar	Bending radius mm	Weight kg/m	Length m	Article number	Stock (n) or min. order m
100	-0/+1	117.0	±1.5	6.0	18	140	3.32	20	5026072	n
								40	5026073	n
125	-0/+2	142.5	±2.0	6.0	18	170	4.1	10	5501457	n
								20	5501458	n
150	-0/+2	167.5	±2.0	6.0	18	200	4.97	10	5501459	n
								20	5501460	n

Branding



and embossed: TRELLEBORG - - FDA - WP 6 bar - week/year - Made in France

