


VENDANGE

AGRI & FOOD

Foodstuff transfer



Applications

Specially designed for transfer of fresh grapes in wine processing industries.

Advantages

- Outstanding flexibility and easy handling.
- ID 125 mm: weak tractive effort thanks to slicking cover.
- Smooth, seamless, white tube, that does not propagate bacterial growth.
- Resistant to cleaning with detergent or steam at temperatures up to 110 °C (during 10 minutes max).
- Non marking cover.
- Contains no phthalate.

Technical description

Inner tube: food grade quality NR, white, smooth.

Reinforcement: synthetic textile with embedded steel helix.

Cover: NR, brick-red, fabric impression, corrugated.

For ID 125 mm: special polymer-based additional film for slicking.

Temperature range: - 30 °C to + 80 °C.

Standard/Approval:

FDA regulation 21 CFR 177.2600.

French legislation.

All relevant migrations tests (France and FDA) were performed and confirmed compliant by the French institute of Poitiers (IANESCO).

Couplings/Fittings

Specially designed fittings are available, please contact us for further information in order to get optimum connections.

VENDANGE

08/12/2009

ID		OD		Working pressure	Bursting pressure	Bending radius	Weight	Length	Article number	Stock (■) or min. order
mm		mm		bar	bar	mm	kg/m	m		m
100.0	- 0/+ 1	117.0	± 1.5	6	18	140	3.32	20	5026072	■
								40	5026073	■
125.0	- 0/+ 2	142.5	± 2.0	6	18	170	4.10	10	5501457	■
								20	5501458	■
150.0	- 0/+ 2	167.5	± 2.0	6	18	200	4.97	10	5501459	■
								20	5501460	■

Branding



and embossed: TRELLEBORG - VENDANGE - FDA - WP 6 bar - week/year - Made in France

