



Applications



Earthmover Radial Tires

PREMIUM CONSTRUCTION PNEUMATIC

EMR 1050

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability while the multi surface tread design delivers control and perfect grip when it's needed the most, whether on sand, rock, gravel or soil.

The strong radial carcass and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption.

Designed for loader applications, the EMR 1050 range is the best solution for open pits and quarries, underground mines, waste and recycling as well as severe construction applications.

Tire Features



PREMIUM CONSTRUCTION PNEUMATIC

EMR 1050

LOADER SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (32/nds)	Service Description LI/SS Loader	Tire Load Capacity (lbs) at 6 (mph)	Tire Pressure (PSI)
20.5 R 25	L5	17.00/2.0-25 (17.00/1.7-25)	107	** 193 A2	25,353	83
23.5 R 25	L5	19.50/2.5-25	113	** 201 A2	31,973	83
26.5 R 25	L5	22.00/3.0-25	122	** 209 A2	40,785	83
29.5 R 25	L5	25.00/3.5-25	138	** 216 A2	49,383	83

^{*/**} – Index of tire strength

Main Benefits

- High resistance to external aggression
- Excellent tire life due to deep tread
- Designed for very hard conditions
- Sidewall rubber ring guard

New sidewall protection



