



Tufcote – absorbing foams

Noise, vibration and shock control

Tufcote foams are manufactured using a proprietary thin sheet casting process that chemically bonds the foams to a variety of film facings or to barrier or damping materials to form integrated composite products. Tufcote acoustic absorbing foams are available in a variety of types:

- M-Series foams are formulated specifically for the transportation industry
- E-Series foams are for general OEM use
- H-Series foams feature additional flame retardants
- QUASH self-supporting sound management foams withstand exposure to fluids, grease and oil, Foams can be combined with Tufcote barriers, a variety of functional facings and PSA backing

Benefits:

- Acoustic absorbing foams - widely used to reduce noise levels within an enclosed space
- Available in a variety of protective facings - the versatile foams are available in 3 formulations and can be supplied with a variety of protective facings
- Supplied in rolls, sheets or as custom die-cut parts - available with or without pressure sensitive adhesive (PSA) backing and thicknesses range from 0.25 inches to 2 inches
- Flexible - easy to install

Applications:

Tufcote foams are used in diverse applications, including:

- Vehicle cabs
- Equipment cabinetry

Family	Product	Thick (in)	Roll (in) (unless indicated)	Sheet (in) (unless indicated)	Weight (lb/sq ft)
FACED FOAMS Aluminized Facing X=M,E,H	X-25SM	0.25	54 X 266	54 X 72	0.04
	X-50SM	0.50	54 X 266	54 X 72	0.08
	X-75SM	0.75	54 X 266	54 X 72	0.13
	X-100SM	1.00	54 X 266	54 X 72	0.17
	X-150SM	1.50	54 X 133	54 X 72	0.25
	X-200SM	2.00		54 X 72	0.33
Reinforced Aluminized Facing X=M,E	X-25RM	0.25	54 X 266	54 X 72	0.04
	X-50RM	0.50	54 X 266	54 X 72	0.08
	X-75RM	0.75	54 X 266	54 X 72	0.13
	X-100RM	1.00	54 X 266	54 X 72	0.17
	X-200RM	2.00		54 X 72	0.33
Matte Black Polyurethane Facing	H-50TBK	0.50	54 x 200 ft	54 x 75	0.12
	H-100TBK	1.00	54 x 100 ft	54 x 90	0.2
	H-150TBK	1.50	54 x 50 ft	54 x 90	0.27
	H-200TBK	2.00	54 x 50 ft	54 x 90	0.34
Black Urethane Facing X=M,E	X-50BU	0.50	54 X 266	54 X 74	0.08
	X-75BU	0.75	54 X 266	54 X 74	0.13
	X-100BU	1.00	54 X 266	54 X 74	0.17
	X-200BU	2.00		54 X 74	0.33
Clear Poly. Facing X=M,E	X-100CM	1.00	54 X 266	54 X 72	0.17


Family	Product	Thick (in)	Roll (in) (unless indicated)	Sheet (in) (unless indicated)	Weight (lb/sq ft)
TEXTURED SURFACE	E-25TF	0.25	54 x 60 ft		0.04
FOAMS	E-50TF	0.50	54 X 60 ft		0.08
Polyester	E-75TF	0.75	54 X 60 ft		0.13
	E-100TF	1.00	54 X 60 ft		0.17
Polyether	X-25SF	0.25	54 X 266	54 X 72	0.04
X=M,E,H	X-50SF	0.50	54 X 266	54 X 72	0.08
	X-75SF	0.75	54 X 266	54 X 72	0.13
	X-100SF	1.00	54 X 266	54 X 72	0.17
PLAIN FOAMS	E-25	0.25	54 X 60 ft		0.04
	E-50	0.50	54 X 60 ft		0.08
	E-75	0.75	54 X 60 ft		0.13
	E-100	1.00	54 X 60 ft		0.17

Contact Us

Trelleborg Applied Technologies delivers innovative and reliable solutions that maximize business performance to meet your needs. Our dedicated and highly skilled staff are always on hand to provide seamless process support from initial idea, through to delivery and beyond.

Tel: +44 (0) 1777 712500

Email: appliedtechnologies@trelleborg.com



WWW.TRELLEBORG.COM/APPLIED-TECHNOLOGIES

