



# EMR 1050 Earthmover Radial Tires

PREMIUM RADIAL PNEUMATIC

The Trelleborg EMR range is designed to enhance productivity in critical construction applications, delivering both enhanced damage protection and durability while the multi surface tread design delivers control and perfect grip when it's needed the most, whether on sand, rock, gravel or soil.

The strong radial carcass and state of the art compound assure long life, while providing equal load distribution for a comfortable ride, maintaining low fuel consumption.

Designed for loader applications, the EMR 1050 range is the best solution for open pits and quarries, underground mines, waste and recycling as well as severe construction applications.

### **Main Benefits**

**Tire Features** 

- High resistance to external aggression
- · Excellent tire life due to deep tread
- · Designed for very hard conditions
- Sidewall rubber ring guard

### **Applications**



1 EXCELLENT RIDE COMFORT RADIAL CONSTRUCTION REINFORCED CARCASS MULTI SURFACE


# EMR 1050 PREMIUM RADIAL PNEUMATIC

## LOADER SERVICE

Tire Size	Tread Pattern TRA	Rim Size (Permitted)	Tread Depth (mm)	Service Description LI/SS Loader	Tire Load Capacity (kg) at 10 (Km/h)	Tire Pressure (bar)
20.5 R 25	L5	17.00/2.0-25 (17.00/1.7-25)	85	** 193 A2	11,500	5.75
23.5 R 25	L5	19.50/2.5-25	90	** 201 A2	14,500	5.75
26.5 R 25	L5	22.00/3.0-25	97	** 209 A2	18,500	5.75
29.5 R 25	L5	25.00/3.5-25	110	** 216 A2	22,400	5.75

\*/\*\* - Index of tire strength

## New sidewall protection





Follow us

Yokohama TWS S.p.A. Via Nazionale Tiburtina, 143 - 00019 Villa Adriana - Tivoli (RM), Italy Phone: +39 0774 3841 – info.tws@yokohama-tws.com www.trelleborg-tires.com

