

FluoroSeal 350 — Industrial Grade

Gasket sheet manufactured from a blend of fluoroelastomer polymer and polyacrylates. Economically designed for applications that require 350° F service temperature and good chemical resistance.

Physical Property	Test Method	Typical Values
Service Temperature		-20 to 350° F
Hardness Durometer (Shore A)	ASTM D 2240/DIN 53505	75 (±5)
Tensile Strength	ASTM D 412/DIN 53504	1200 psi
Average Elongation	ASTM D 412/DIN 53504	225%
Specific Gravity	ASTM 792	1.76

FluoroSeal Gasket Sheet Styles and Sizes

Products sold by square yard or linear yard x 48" width. Custom sizes available on request. RESTRICTIONS: Fluoroelastomers are not generally resistant to ketones, low molecular weight esters (such as ethyl acetate), or nitro hydrocarbons.

Grade	Thicknesses	Widths	Finishes
FluoroSeal 350	1/16", 1/8", 3/16", 1/4", 1/2"	36" or 48"	Fabric or smooth
FluoroSeal 400	1/16", 1/8", 3/16", 1/4", 1/2"	36" or 48"	Fabric or smooth
FluoroSeal 450	1/16", 1/8", 3/16", 1/4", 1/2"	36" or 48"	Fabric or smooth

High Quality Industrial Fabrics and Composites from Trelleborg

- EPDM sheet rubber
- Silicone sheet rubber
- PTFE coated fabrics and tapes
- Silicone coated fabrics
- Specialty belting
- Flue duct expansion joint materials
- Elastomer coated and calendered fabrics
- Fiberglass insulation matting
- Film and foil laminates
- Safety clothing and welding curtain fabrics