



Trelleborg HANK™

**High
Abrasion
Neoprene
Kevlar**



APPLICATION(S)

HANK™ is designed to meet the needs of defense, first responders, homeland security and special operations.

Waterproof and abrasion-resistant HANK™ also features a system that no longer requires MOLLE, a modularity system for attaching gear.

A simple slit in the HANK™ material provides all the benefits of MOLLE, making it less costly for the end-use manufacturer to produce. Without the additional weight of MOLLE, the wearer can move more quickly.

KEY CHARACTERISTICS

- 10 oz., 18 oz., 25 oz., or 35 oz. options
- Lightweight
- Excellent abrasion resistance
- Water resistant
- Flexible
- Made in the USA
- Berry Compliant

HANK™ flexes its muscles in a variety of colors, including camo green, ranger green, black, gray and coyote brown. Multiple color combinations are available.

Trelleborg

HANK™

**High
Abrasion
Neoprene
Kevlar**



PROPERTIES	TEST METHOD	REQUIREMENTS
Width	ASTM D 751-89, sec. 8	60" (+/-1") trimmed
Total Weight	ASTM D 751-89, sec. 10.2	10.00 Nominal oz/sq yd
Adhesion	ASTM D 751-89, sec. 43.1.2	a. Min. of 8 lbf./in.
Flame Resistance a. Flame, Fill b. Flame, Warp c. Char, Fill d. Char, Warp	Fed Std 191A, Method 5903	a. Max 5 inches b. Max 30 seconds c. Max 5 inches d. Max 30 seconds
Grab Tensile a. Fill b. Warp	ASTM D 751-89, sec. 111	a. Min. of 100 lb. b. Min. of 100 lb.
Taber Abrasion	ASTM D 3389-94, Method A	Min. of 50.00 cycles

This data is for 10 oz. Coyote Brown/Black. Data varies by color.