

TM600. Reliability at first sight.



Download the App for free



Tire iBrochure

TM600 Reliability at first sight.

The TM600 range has been developed using the lightest materials possible while maintaining outstanding strength and durability.

The range is ideal for medium powered tractors.




Printed on
recycled paper

Excellent traction for maximum crop protection

The shape, geometry, number and depth of the TM600 lug's have been carefully designed in order to guarantee excellent traction in all soil conditions.

The chart shows the higher traction capability of the Trelleborg TM600 tires compared to the same sizes of premium brand competitors.

TRACTION IN FIELD
Slippage: 10-15%



Minimum soil compaction, maximum lightness



The TM600 ensures uniform soil penetration and high flotation performance, helping to reduce compaction, thus protecting the soil and enhancing fertility.

In order to achieve these benefits, the contact patch has been designed to spread the load equally and minimizing the contact pressure in the center of the tread.

FOOTPRINT AREA Size: 520/85R38 - Load: 8,543 lb

+24%



TM600
489 inches²




Premium Competitor A
427 inches²




Premium Competitor B
374 inches²

Higher is
better



The rounded shoulder of the lug has been designed to minimize damage to grass and crops as well as maintaining good lateral stability and traction.



The geometry of the inter-lug terraces enhances the self-cleaning characteristics on muddy soil.




Exceptional comfort

Today tractors are increasingly used on the road moving quickly from one field to another, often carrying equipment or towing trailers. Over the years, the TM600 has not only proved

great performance in the fields, but also on the road, ensuring high comfort throughout the complete life of the tire.

COMFORT PERFORMANCE

Size front: 380/85R28 - Size rear: 460/85R38




In addition to excellent driver comfort, the TM600 provides excellent handling performance. It also provides exceptional steering and cornering characteristics.

As a result of driving and handling tests among end-users, the TM600 has been selected as best among premium competitors.

HANDLING PERFORMANCE

Size rear: 460/85R38



SIZE	Tread Pattern	SW Inches	OD Inches	SLR Inches	RC Inches	SRI	Rim	Permitted Rims	Type	Tube
210/95R16 106A8 (106B)	TM600	8.3	31.5	14.3	95.1	390	W7	W6 - 5.50F	TUBELESS	
210/95R18 108A8 (108B)	TM600	8.3	33.7	15.4	100.6	410	W7	W6 - 5.50F	TUBELESS	
280/85R20 112A8 (109B) (11.2R20)	TM600	11.6	38.8	17.7	116.3	475	W10	W9 - W8 - DW10	TUBELESS	11.2-20 TR218
320/85R20 119A8 (116B) (12.4R20)	TM600	13	41.4	18.5	124.4	500	W11	W10 - W9 - DW11	TUBELESS	11.2-20 TR218
250/85R24 112A8 (109B)	TM600	9.6	40.7	18.3	122.6	500	W8	W7 - W9	TUBELESS	9.5-24 TR218
280/85R24 115A8 (112B) (11.2R24)	TM600	11.5	42.8	19.4	129	525	W10	W9 - W8 - DW10	TUBELESS	11.2-24 TR218
320/85R24 122A8 (119B) (12.4R24)	TM600	13	45.4	20.3	136.4	550	W11	W10 - W9 - DW10 DW11	TUBELESS	12.4/13.6-24 TR218
340/85R24 125A8 (122B) (13.6R24)	TM600	13.9	46.8	21.3	139.6	575	W12	W11 - DW11 - DW12	TUBELESS	13.6/14.9-24 TR218
380/85R24 131A8 (128B) (14.9R24)	TM600	15.4	49.4	22	147.6	600	W13	W12 - W11 - DW11 DW12 - DW13	TUBELESS	14.9/16.9-24 TR218
420/85R24 137A8 (134B) (16.9R24)	TM600	17.2	52.1	23.2	156.3	625	W15L	W14L - DW14L DW15L	TUBELESS	16.9-24 TR218
280/85R28 118A8 (115B) (11.2R28)	TM600	11.5	46.7	21.3	140.9	575	W10	W9 - DW10	TUBELESS	11.2/12.4-28 TR218
320/85R28 124A8 (121B) (12.4R28)	TM600	13	49.4	22.3	149.4	600	W11	W10 - W9 - DW10 DW11	TUBELESS	12.4-28 TR218
340/85R28** 127A8 (124B) (13.6R28)	TM600	13.9	50.7	23.4	153	625	W12	W11 - DW11 - DW12	TUBELESS	13.6/12.4-28 TR218
380/85R28 133A8 (130B) (14.9R28)	TM600	15.4	53.4	24.2	160.8	650	W13	W12 - W11 - DW11 DW12 - DW13	TUBELESS	14.9/16.9-28 TR218
420/85R28** 139A8 (136B) (16.9R28)	TM600	17.2	56.1	25	168.9	675	W15L	W14L - DW14L DW15L	TUBELESS	16.9-28 TR218
380/85R30 135A8 (135B) (14.9R30)	TM600*	15.4	55.4	25	166.9	675	W13	W12 - W11 - DW11 DW12 - DW13	TUBELESS	14.9-30 TR218
420/85R30** 140A8 (137B) (16.9R30)	TM600	17.2	58.1	26	175.4	700	W15L	W14L - DW14L DW15L	TUBELESS	16.9/18.4-30 TR218
420/90R30 147A8 (147B)	TM600	17.1	59.8	27.2	180.3	700	DW13	W13 - W14L - DW14L	TUBELESS	18.4-30 TR218
460/85R30 145A8 (142B) (18.4R30)	TM600	18.7	60.8	27.2	184.2	725	W16L	W15L - DW15L DW16L	TUBELESS	18.4-30 TR218
380/85R34 142A8 (142B) (14.9R.3A)	TM600	15.4	59.6		179.7	725	W12	W13	TUBELESS	
420/85R34 147A8 (147B)	TM600	17.5	62	28.5	186.4	750	W15L	W14L - DW14L DW15L	TUBELESS	16.9-34 TR218
460/85R34 147A8 (144B)	TM600	18.7	64.8	29.3	194.7	775	W16L	W15L - DW15L DW16L	TUBELESS	18.4/16.9-34 TR218
320/85R38 129A8 (126B) (12.4R38)	TM600	12.8	59.8	27.2	181.3	725	W11	W10 - W9 - DW10 DW11	TUBELESS	12.4/16.9-38 TR218
340/85R38 133A8 (130B) (13.6R38)	TM600	13.9	60.7	28	183.7	750	W12	W11 - DW11 DW12	TUBELESS	13.6/16.9-38 TR218
380/80R38 142A8 (142B)	TM600	14.8	62	28.5	187.6	750	W12	W11 - W13 DW11 - DW12 - DW13	TUBELESS	14.9/16.9-38 TR218
380/85R38 144A8 (144B) (14.9R38)	TM600	15.7	63.4	28.7	192.9	775	W13	W11 - W12 DW11 - DW12 - DW13	TUBELESS	16.9-38 TR218
380/95R38 147A8	TM600*	15.4	65.9	30	197.6	800	W12	W13	TUBELESS	
400/75R38 138A8 (135B) (15.5R38)	TM600	15.6	61.6	27.8	183.9	750	DW14L	W14L	TUBELESS	16.9-38 TR218
420/85R38 144A8 (141B) (16.9R38)	TM600	17.2	66.1	29.9	199.2	800	W15L	W14L - DW14L DW15L	TUBELESS	16.9-38 TR218
420/85R38 149A8	TM600*	17.3	65.6	30.2	196.9	800	W14L	DW14L - W15L DW15L	TUBELESS	
460/85R38** 149A8 (146B) (18.4R38)	TM600	18.7	68.8	31.5	207.1	825	W16L	W15L - DW15L DW16L	TUBELESS	18.4-38 TR218
480/80R38 149A8 (149B)	TM600*	19.5	69.3	30.9	206.1	825	W16A	W15L - DW15L DW16L		
520/85R38 155A8 (152B) (20.8R38) Design data	TM600*	22.1	72.8	32.3	218.5	875	DW18L	W16L - W18L DW16L	TUBELESS	20.8-38 TR218
520/85R38** 155A8 (152B) (20.8R38)	TM600	21.1	72.8	32.5	216.9	875	DW18L	W16L - W18L DW16L	TUBELESS	20.8-38 TR218
480/80R42** 151A8 (151B) (18.4R42)	TM600	19.5	72.8	32.8	218.5	875	W16A	DD16 - DW16B - DW16L	TUBELESS	18.4/20.8-42 TR218
520/85R42** 157A8 (157B)	TM600	21.1	76.9	34.7	231	925	DW18L	W16L-W18L-DW16L	TUBELESS	20.8-42 TR218
480/80R46 158A8 (158B) (18.4R46)	TM600	19.5	77.36	34.9	234.3	925	W16A	DD16 - DW16B	TUBELESS	
520/85R46 158A8 (158B) (20.8R46)	TM600	21.1	80.5	35.6	242.5	975	DW16L	W16L - W18L - DW16L DD16L - DD18L	TUBELESS	
480/80R50 159D	TM600	19.7	80.5	36.8	243.7	975	DW15B	DW16B	TUBELESS	
480/80R50 159A8 (159B)	TM600 Rice*	19.3	80.5		243.5	975	DW15B		TUBELESS	
480/95R50 164A8 (164B)	TM600*	19.7	84.6	38.7	255.5	1075	DW16B	DW16A - DW15A - DW15B	TUBELESS	

* = ProgressiveTraction® version
 ** = Available also in HD version



Trelleborg is a world leader in engineered polymer solutions that seal, damp and protect critical applications in demanding environments. Our innovative engineered solutions accelerate performance for customers in a sustainable way. The Trelleborg Group has local presence in over 50 countries around the world.

WWW.TRELLEBORG.COM/WHEELS



facebook.com/TrelleborgAgri
twitter.com/TrelleborgWheel
youtube.com/TrelleborgAgri
flickr.com/TrelleborgAgri
linkedin.com/company/trelleborgwheelsystems
instagram.com/TrelleborgAgri



Trelleborg Wheel Systems Americas, Inc
570 Trelleborg Drive, Spartanburg, SC 29301
Toll Free Phone Number: 1-866-633-8473
www.trelleborg.com/wheels/us