




Smooth shank

DIN 2817/DIN EN 14 420-5

DOUILLE LISSE CAÑA LISA

Smooth shank DIN 2817/DIN EN 14 420-5




MATERIAL MATIÈRE MATERIAL

- AL** = Aluminium
- BR** = Brass **Laiton Latón**
- ST** = Steel **Acier Acero**
- SS** = Stainless steel **Inox**
- PP** = Polypropylene

SIZE DIMENSIONS DIMENSIONES

From DN 13 to 150 mm



DN
13
19
25
32
38
50
65
75
100
125
150



■ AL = Aluminium
 ■ BR = Brass *Laiton Latón*
 ■ ST = Steel *Acier Acero*
 ■ SS = Stainless steel *Inox*
 ■ PP = Polypropylene

Trelleborg Fittings 2015

		ID coupling Diam. raccord Diam. racor	ID shank Diam. douille Diam. espiga	Ref.	Notes
 <p>Female thread. Fileté femelle. <i>Rosca hembra.</i></p>	SS 316L	1/2"	13	510 91 24	
		3/4"	19	010 00 08	
		1"	25	010 00 09	
		1"1/4	32	010 00 10	
		1"1/2	38	010 00 11	
		2"	50	010 00 12	
		2"1/2	63	010 00 13	
		3"	75	010 00 14	
 <p>Male thread. Fileté mâle. <i>Rosca macho.</i></p>	SS 316L	4"	100	510 01 71	
		1/2"	13	510 91 25	
		3/4"	19	010 00 01	
		1"	25	010 00 02	
		1"1/4	32	010 00 03	
		1"1/2	38	010 00 04	
		2"	50	010 00 05	
		2"1/2	63	010 00 06	
 <p>Female thread. Fileté femelle. <i>Rosca hembra.</i></p>	BR	3"	75	010 00 07	
		4"	100	510 01 70	
		3/4"	19	510 02 27	
		1"	25	510 02 28	
		1"1/4	32	500 50 02	
		1"1/2	38	510 02 29	
		2"	50	510 02 30	
		2"1/2	63	510 01 20	
 <p>Male thread. Fileté mâle. <i>Rosca macho.</i></p>	BR	3"	75	510 02 31	
		4"	100	510 02 42	
		3/4"	19	510 16 43	
		1"	25	510 01 75	
		1"1/4	32	010 00 30	
		1"1/2	38	010 00 32	
		2"	50	010 01 20	
		2"1/2	63	011 81 69	
 <p>Male thread. Fileté mâle. <i>Rosca macho.</i></p>	PP	3"	75	510 01 76	
		4"	100	510 01 77	
		1"	25	510 01 73	
		1"1/2	38	510 01 74	
		2"	50	010 01 33	
		3"	75	010 01 34	

AL = Aluminium BR = Brass Laiton Latón ST = Steel Acier Acero SS = Stainless steel Inox PP = Polypropylene

Trelleborg Fittings 2015

		ID coupling Diam. raccord Diam. racor	ID shank Diam. douille Diam. espiga	Ref.	Notes
 <p>Camelock. Coupler. Camelock. Coupleur. Camelock. Acoplador.</p>		SS 316	20	20	510 01 04
			25	25	510 02 32
			32	32	510 02 34
			40	38	010 00 62
			50	50	510 01 33
			65	63	510 02 37
			80	75	510 02 39
			100	100	510 02 41
 <p>Camelock. Adapter. Camelock. Adapteur. Camelock. Adaptor.</p>		SS 316	20	20	510 01 03
			25	25	510 02 33
			32	32	510 02 35
			40	38	510 02 36
			50	50	510 01 34
			65	63	510 02 38
			80	75	510 02 40
			100	100	011 78 63
 <p>Loose flange. Bride tournante. Brida giratoria.</p>	PN 10-40.	SS 316	40	38	510 18 52
	PN 10-16.		50	50	510 18 53
	PN 10-16.		65	63	510 18 54
	PN 10-16.		80	75	510 18 55
	PN 10-16.		100	100	510 18 56
	PN 10-16.		150	150	510 27 82
	PN 10-40.	ST	40	38	510 18 57
	PN 10-16.		50	50	510 18 58
	PN 10-16.		65	63	510 18 59
	PN 10-16.		80	75	510 18 60
	PN 10-16.		100	100	510 18 61
	PN 10-16.		150	150	510 18 62
 <p>Storz Type C. Storz Type B. Storz Type A.</p>		AL	52	50	510 50 98
			75	75	510 50 99
			110	100	510 51 00




■ AL = Aluminium
 ■ BR = Brass *Laiton Latón*
 ■ ST = Steel *Acier Acero*
 ■ SS = Stainless steel *Inox*
 ■ PP = Polypropylene

Trelleborg Fittings 2015

		ID coupling Diam. raccord Diam. racor	ID shank Diam. douille Diam. espiga	Ref.	Notes
 <p>DIN 11851 Female. With collar. DIN 11851 Femelle. A collerette. <i>DIN 11851 Hembra. Con cuello.</i></p>	SS 316L	40	38	010 01 32	
		50	50,5	510 00 70	
		65	63	510 02 23	
		80	75	510 02 24	
 <p>Nut. DIN 11851. Ecrou. DIN 11851. <i>Tuerca. DIN 11851.</i></p>	SS 304	40		011 69 34	
		50		011 67 39	
		65		011 69 10	
		80		011 69 13	
 <p>DIN 11851 Male. With collar. DIN 11851 Mâle. A collerette. <i>DIN 11851 Macho. Con cuello.</i></p>	SS 316L	40	38	510 02 69	
		50	50,5	510 07 00	
		65	63	510 18 50	
		80	75	510 18 51	
 <p>SMS 1145 Female. With collar. SMS 1145 Femelle. A collerette. <i>SMS 1145 Hembra. Con cuello.</i></p>	SS 316L	25	25	500 50 04	
		38	38	500 50 06	
		51	50,5	500 50 08	
		63	63	510 18 48	
 <p>Nut. SMS 1145. Ecrou. SMS 1145. <i>Tuerca. SMS 1145.</i></p>	SS 304	25		011 69 78	
		38		011 68 72	
		51		011 68 62	
		63		011 68 65	
 <p>SMS 1145 Male. With collar. SMS 1145 Mâle. A collerette. <i>SMS 1145 Macho. Con cuello.</i></p>	SS 316L	25	25	500 50 03	
		38	38	500 50 05	
		51	50,5	500 50 07	
		63	63	510 18 49	

AL = Aluminium BR = Brass Laiton Latón ST = Steel Acier Acero SS = Stainless steel Inox PP = Polypropylene

Trelleborg Fittings 2015

		OD ferrule clamp Diam. ext. ferrule Diam. ext. clamp	ID shank Diam. douille Diam. espiga	Ref.	Notes
 <p>TRI CLAMP. With collar. SMS Norm. TRI CLAMP. A collerette. Norme SMS. TRI CLAMP. Con cuello. Norma SMS.</p>	SS 316L	50,5	25	510 05 46	
		50,5	38	510 05 47	
		64	50	510 05 94	
		77,5	63	510 05 95	
		91	75	510 05 96	
 <p>Clamp. TRI CLAMP. Collier. TRI CLAMP. Abrazadera. TRI CLAMP.</p>	SS 304	50,5		011 82 27	
		64		011 80 97	
		77,5		011 82 28	
		91		011 82 29	
 <p>For welding. With collar. A souder. A collerette. Para soldar. Con cuello.</p>	SS 316	13	13	510 70 33	
		16	16	510 70 34	
		19	19	510 70 35	
		25	25	510 70 36	
		32	32	510 70 37	
		38	38	510 70 38	
		51	51	510 70 39	
		63	63	510 70 40	
		75	76	510 70 41	
102	102	510 70 42			

AL = Aluminium BR = Brass Laiton Latón ST = Steel Acier Acero SS = Stainless steel Inox PP = Polypropylene

Trelleborg Fittings 2015

		ID coupling Diam. raccord Diam. racor	ID shank Diam. douille Diam. espiga	Ref.	Notes
	13 * 5	22 - 24	13	011 75 61	
	19 * 6	30 - 33	19	011 34 72	
	25 * 6	36 - 39	25	073 20 19	
	25 * 8	40 - 43	25	011 75 62	
	32 * 6	43 - 46	32	073 20 20	
	32 * 8	47 - 50	32	011 75 63	
	38 * 5	47 - 49	38	510 89 77	
	38 * 6,5	50 - 52	38	073 16 63	
	38 * 8	53 - 56	38	011 17 49	
	38 * 10	57 - 60	38	011 20 11	
	50 * 6	61 - 63	50	510 10 18	
	50 * 8	64 - 67	50	073 16 64	
	50 * 10	69 - 71	50	011 18 86	
	63 * 6	74 - 76	65	510 29 76	
	63 * 8 - 65 * 7	78 - 82	65	011 17 50	
	65 * 10	84 - 87	65	011 18 91	
	75 * 8	89 - 93	75	073 16 66	
	75 * 10	94 - 97	75	073 20 12	
	75 * 12	98 - 101	75	011 75 64	
	80 * 8	94 - 97	80	011 17 51	
	80 * 10	99 - 102	80	011 18 95	
	100 * 8	114 - 119	100	073 16 67	
	100 * 10	118 - 122	100	011 18 99	
	100 * 12	122 - 126	100	011 12 49	
	100 * 14	126 - 130	100	011 15 82	
	100 * 16	130 - 134	100	011 36 52	
	125 * 10	143 - 148	125	011 17 52	
	125 * 15	153 - 158	125	011 75 65	
	150 * 13	174 - 180	150	011 75 66	
	150 * 15	178 - 184	150	011 17 54	
	150 * 10	168 - 174	150	011 17 53	
	200 * 12	222 - 229	200	011 17 56	



DIN 2817.
Safety Clamp
Collier 1/2 coquille.
Abrazadera 2 mitades
DIN 2817.

AL

■ AL = Aluminium
 ■ BR = Brass **Laiton Latón**
 ■ ST = Steel **Acier Acero**
 ■ SS = Stainless steel **Inox**
 ■ PP = Polypropylene

Trelleborg Fittings 2015



DIN 2817.
 Safety Clamp
Collier 1/2 coquille.
Abrazadera 2 mitades
DIN 2817.

ID coupling
Diam. raccord
Diam. racor

ID shank
Diam. douille
Diam. espiga

Ref.

Notes

		ID coupling Diam. raccord <i>Diam. racor</i>	ID shank Diam. douille <i>Diam. espiga</i>	Ref.	Notes
	13 * 5	22 - 24	13	011 75 67	
	19 * 6	30 - 33	19	011 75 68	
	25 * 6	36 - 39	25	011 75 69	
	32 * 6	43 - 46	32	011 75 70	
	38 * 6,5	50 - 52	38	011 75 71	
	50 * 6	61 - 63	50	510 89 76	
	50 * 8	64 - 67	50	011 75 72	
	63 * 6	73 - 77	63	510 89 75	
	65 * 7	78 - 82	65	011 75 73	
	75 * 6,5	86 - 90	75	510 31 81	
	75 * 8	89 - 93	75	011 75 74	
	100 * 8	114 - 119	100	011 75 75	
				13 - 38	M6-STOP
				50 - 80	M8-STOP
				100 - 125	M10-STOP
				150 - 200	M12-STOP



Autoblock nut.
Ecrou autobloquant.
Tuerca autoblocante.

SS 316

SS