

GUTTELING CHEM 10 PG



APPLICATIONS

Suction and discharge of a large number of aggressive or corrosive chemicals, chemical waste and all petroleum products with aromatic content up to 100%.
For road and rail tanker equipment or fixed installations in the chemical industry.

ADVANTAGES

- Easy to handle due to hose flexibility (low bending radius).
- Usable at a wide range of temperatures.
- Capable of handling many different chemicals.

COUPLING/FITTINGS

All types of swaged couplings:

- standard or revolving Guillemín
- standard or secured camlock coupling
- threaded male or female fitting (BSP, NPT, etc.)
- fixed or swivel flange ISO PN10/16, PN20 (ASA150), TTMA, etc.

COMPLEMENTARY INFORMATION

Fitted lengths are delivered on request with pressure test certificate.
Imperial size on request.

TECHNICAL DESCRIPTION

Internal helix	polypropylene coated steel.
Inner tube	polypropylene film.
Reinforcement	polypropylene layers
Cover	PVC coated fabric, grey, corrugated.
External helix	galvanized steel.
Working temperature	-30°C => +100°C.
Electrical Properties	resistance between end fittings ≤100Ω/assembly.


STANDARD/APPROVAL

EN 13765: Bureau Veritas type approval N°7232905/8/049/TBE.

EN

-

TMD





ID (MM)	OD (MM)	WORKING PRESSURE (BAR)	BURSTING PRESSURE (BAR)	BENDING RADIUS (MM)	WEIGHT (KG/M)	LENGTH (M)	TYPE	ARTICLE NUMBER
50.0	62.0	10	40	180	1.66	30.0		30103746
65.0	78.5	10	40	200	2.76	30.0		30103891
65.0	78.5	14	56	200		30.0	DRY	30101487
80.0	95.0	10	40	280		30.0		30103600
100.0	118.0	10	40	400	5.16	30.0		30103925
100.0	121.0	14	56	400		30.0	DRY/WET	30101618

Tolerance on length: ±1% (ISO 1307 Standard).