



GUTTELING OIL BLUE



OIL & GAS

Composite hoses/Oil and petroleum



APPLICATIONS

GUTTELING OIL BLUE hoses are designed for conveying hydrocarbons, solvents, 100% aromatics, etc. GUTTELING OIL BLUE hoses are highly flexible and reliable in all kind of transfer operations.

There are three different types, depending on pressure and application, namely:

Light duty	Tank truck and railcar
Standard duty	Tank truck, railcar and in plant transfer
Heavy duty	Heavy duty marine operations and ship and barge loading and unloading

PHYSICAL PROPERTIES

- Maximum elongation: 10% on proof pressure
- Electrical resistance: max. 100 Ohm per length
- Maximum twist: 10° p/m
- Vacuum range: 0,9 bar
- Min. burst pressure: 5x working pressure (safety fact 5:1)
- Max. flowrate: on request
- Max. tensile strength: on request
- Pressure losses: on request
- Temperature range: -30°C up to +100°C (-22F up to +212F)

TECHNICAL DESCRIPTION

Inner wire: Galvanized steel

Lining: Polypropylene

Outer cover: Polyester PVC coated blue

Outer wire: Galvanized steel

STANDARD/APPROVAL


GUTTELING OIL BLUE hoses are produced and tested according international standards like EN 13766 & IMO IGC code.



COMPLEMENTARY INFORMATION

Other outer wire qualities (Aluminum, Polypropylene coated steel, Stainless steel 316/304) are available upon request. Other cover colors available upon request.

Assembled lengths are delivered with pressure test certificate.





Light Duty, 7 bar

Bore diameter		Max. work. pressure		Bend radius		Weight		Maximum length	
inches	mm	PSI	bar	inches	mm	lbs/Ft	Kg/m	Ft	m
1	28	100	7	4,9	125	0,55	0,85	100	30
1,5	40	100	7	5,9	150	0,75	1,15	100	30
2	50	100	7	7,9	200	0,85	1,3	100	30
2,5	65	100	7	8,3	210	1,45	2,2	100	30
3	80	100	7	11,8	300	1,8	2,7	100	30
4	100	100	7	15,7	400	2,95	4,4	100	30

Standard Duty, type 2

Bore diameter		Max. work. pressure		Bend radius		Weight		Maximum length	
inches	mm	PSI	bar	inches	mm	lbs/Ft	Kg/m	Ft	m
1	28	150	10,5	4,9	125	0,65	0,95	100	30
1,5	40	150	10,5	5,9	150	1,15	1,7	100	30
2	50	150	10,5	7,9	200	1,2	1,8	100	30
2,5	65	150	10,5	7,9	200	1,95	2,9	100	30
3	80	150	10,5	11,8	300	2,35	3,5	100	30
4	100	150	10,5	15,7	400	3,65	5,5	100	30

Heavy Duty, type 3

Bore diameter		Max. work. pressure		Bend radius		Weight		Maximum length	
inches	mm	PSI	bar	inches	mm	lbs/Ft	Kg/m	Ft	m
1	28	200	14	4,9	125	0,65	0,95	100	30
1,5	40	200	14	5,9	150	1,15	1,7	100	30
2	50	200	14	7,9	200	1,2	1,8	100	30
2,5	65	200	14	7,9	200	1,95	2,9	100	30
3	80	200	14	13,8	350	3	4,5	100	30
4	100	200	14	15,7	400	5,25	7,9	100	30
5	125	200	14	20,1	510	6,45	9,7	100	30
6	150	200	14	22,6	575	8,25	12,4	100	30
8	200	200	14	31,5	800	14,55	21,8	100	30
10	250	200	14	39,37	1000	17,8	26,7	100	30
12	300	200	14	47,24	1200	21,1	32	82	25

This information is for guidance only, dimensions and weights shown are approximate.

We reserve the right to alter or amend specifications as deemed necessary.

Digital version

