

GUTTELING CHEM 14 SS



**CHEMICALS &
PHARMACEUTICALS**

Composite hoses/Chemical and
corrosive products



APPLICATIONS

Suction and discharge of a large number of aggressive or corrosive chemicals, chemical waste and all petroleum products with aromatic content up to 100%.
For road and rail tanker equipment or fixed installations in the chemical industry.

ADVANTAGES

- _ Easy to handle due to hose flexibility (low bending radius).
- _ Usable at a wide range of temperatures.
- _ Capable of handling many different chemicals.

COUPLING/FITTINGS

All types of swaged couplings:

- standard or revolving Guillemín
- standard or secured camlock coupling
- threaded male or female fitting (BSP, NPT, etc.)
- fixed or swivel flange ISO PN10/16, PN20 (ASA150), TTMA, etc.

COMPLEMENTARY INFORMATION

Fitted lengths are delivered on request with pressure test certificate.
Imperial size on request.

TECHNICAL DESCRIPTION


Internal helix	stainless steel 304L (stainless steel 316L on request).
Inner tube	polypropylene film.
Reinforcement	polypropylene layers
Cover	PVC coated fabric, grey, corrugated.
External helix	stainless steel.
Working temperature	-30°C => +100°C.
Electrical Properties	resistance between end fittings ≤100Ω/assembly.


STANDARD/APPROVAL

EN 13765: Bureau Veritas type approval N°7232905/8/049/TBE.

EN

TMD



CHEMICALS & PHARMACEUTICALS		GUTTELING CHEM 14 SS					
ID (MM)	OD (MM)	WORKING PRESSURE (BAR)	BURSTING PRESSURE (BAR)	BENDING RADIUS (MM)	WEIGHT (KG/M)	LENGTH (M)	ARTICLE NUMBER
25.0	37.0	14	56	100	0.86	30.0	30103981
32.0	43.0	14	56	120	1.10	30.0	30103656
40.0	52.0	14	56	140	1.56	30.0	30103723
50.0	62.0	14	56	180	1.86	30.0	30103724
65.0	78.5	14	56	200	3.03	30.0	30104147
80.0	95.0	14	56	280	3.33	30.0	30103804
100.0	121.0	14	56	400	5.46	30.0	30103821

Tolerance on length: ±1% (ISO 1307 Standard).