

PERFORMER BEND 90°

CONSTRUCTION & MINING EQUIPMENT

Abrasive materials hydraulic and pneumatic handling

PERFORMER bends are used when the bending radius of PERFORMER hose is too large for installation.

Advantages

- Very low bending radius.
- Excellent resistance to abrasion.
- Compensate the misalignments thanks to the flexibility of rubber.
- Damping of vibrations and noise.

Technical description

Inner tube: wear resistant NR, black, smooth.

Reinforcement: synthetic textile with embedded steel helix.


Cover: wear resistant EPDM, black, smooth, corrugated ends.

Temperature range: -30°C to +70°C.

Couplings/Fittings

Hoses have to be fitted with BLOC-END® couplings.

BLOC-END® couplings are sold separately.



ID mm	OD mm	Tube thickness mm	Working pressure bar	Bursting pressure bar	Bending radius mm		A mm	B mm	Weight kg/m	Article number
51	83	8.5	10	30	153	3 x ID	260	105	1.8	5513340
63	98	8.5	10	30	189	3 x ID	285	105	2.5	5513341
76	113	8.5	10	30	228	3 x ID	335	105	3.4	5513342
102	133	8.5	10	30	306	3 x ID	455	213	6.5	5513343
127	158	8.5	10	30	381	3 x ID	570	214	9	5513344
152	183	8.5	10	30	456	3 x ID	670	217	11.7	5513345
204	234.5	8.5	5	15	612	3 x ID	890	270	21.5	5513346
254	285.5	8.5	5	15	762	3 x ID	980	275	33	5513347
305	340.5	8.5	5	15	915	3 x ID	1170	255	49.3	5513348
355	391	8.5	5	15	850	2.4 x ID	1145	295	60.6	5513349
406	441	8.5	5	15	610	1.5 x ID	1090	400	75	5513350

Branding



Non stock article.